



GE
Lighting

12598 - GE Multi-Vapor® PulseArc® Quartz Metal Halide BD17

MVR150/U/MED

Product Photo



GENERAL CHARACTERISTICS

| | |
|---------------------------------|--------------------------|
| Base Description | Medium Screw |
| Base Temp C-degrees (MAX) | 210 °C |
| Base Type | Screw-In |
| Bulb Temperature C-degree(MAX) | 400 °C |
| Lamp Enclosure Type (LET) | Enclosed fixtures only |
| Mercury-Picogram per mean lm hr | 68.6 |
| Rated Life Hours-nominal | 15000 h |
| Bulb Finishes and Colors | Clear |
| Mercury Content EMEA ONLY | 10.8 |
| Bulb Material | Hard glass |
| Product Technology | High Intensity Discharge |
| Base | E26 |
| Bulb Shape | BD17 |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------|----------|
| Mean Lumens nominal | 10500 lm |
| Nominal Lumens per Watt | 93 lm |
| Initial Lumens-nominal | 14000 lm |
| Color Rendering Index-CRI | 65 |
| Color Temperature | 4300 K |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 12598 |
| Description | MVR150/U/MED |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168125987 |
| Standard Package GTIN | 10043168125984 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168125987 |

DIMENSIONS

| | |
|--------------------------------|---------|
| Diameter | 2.12 in |
| Light Center Length Millimeter | 3.43 in |

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|----------------------------|
| Burn Position | Universal burning position |
| Rated power (Watts) | 150 W |

CAUTIONS & WARNINGS

WARNING: This lamp can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured, and the arc tube continues to operate. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain types of lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available. Visit the FDA website for more information: <http://www.fda.gov/cdrh/radhealth/products/urburns.html>

Caution

Lamp may shatter and cause injury if broken

Dispose of lamp in a closed container.

Do not use excessive force when installing lamp.

Do not use lamp if outer glass is scratched or broken.

Do not stare at light source. May be harmful to the eyes. Not applicable to diffuse coated bulbs.

Wear safety glasses and gloves when handling lamp

Warning

A damaged lamp emits UV radiation which may cause eye/skin injury

Turn power off if glass bulb is broken. Remove and dispose of lamp.

Risk of Burn

Allow lamp to cool before handling.

Do not turn on lamp until fully installed.

Risk of Electric Shock

- Do not use where directly exposed to water or outdoors without an enclosed fixture.
- Turn power off before inspection, installation or removal.

Unexpected lamp rupture may cause injury, fire, or property damage

- Do not exceed rated voltage.
- Do not turn on lamp until fully installed.
- Do not use beyond rated life. Beyond rated life, light output diminishes while energy consumption and risk of lamp rupture increases.
- Do not use lamp if outer glass is scratched or broken
- Do not use where directly exposed to water or outdoors without an enclosed fixture
- Turn lamp off at least once for 15 minutes per week. FAILURE TO COMPLY INCREASES THE RISK OF RUPTURE.
- Lamps with E-rated ANSI codes must be operated in enclosed fixtures, see Instructions
- Do not store flammable materials near/below S-rated lamp in open fixture
- Use only properly rated ballast
- Operate lamp only in specified position
- If used on a dimming system, see instructions.

Risk of Fire

- Keep combustible materials away from lamp.
- Use in fixture rated for this product.

Instructions:

LAMP OPERATING CHARACTERISTICS: This is a discharge lamp and requires some time to restart and come to full brightness after a power interruption.

RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Beyond rated life, light output diminishes while energy consumption and risk of lamp rupture increases.

SPECIFIED OPERATING POSITIONS

- VBU - Base up ± 15 degrees
- VBD - Base down ± 15 degrees
- HOR - Horizontal ± 15 degrees
- U - Universal

All lamps are rated for enclosed fixtures, except lamps with S-rated ANSI codes operated in vertical position only (Base Up or Base Down), ± 15 degrees, can be used in an open fixture.

Match ANSI code of lamp to code on ballast or luminaire.

Use in luminaire which comply with UL1598 or IEC 60598. When used, fixture lens/diffuser material must be able to contain fragments of hot quartz or glass (up to 1100 Centigrade).

FOR USE ON DIMMING SYSTEMS - Contact your local GE Lighting sales representative



