



TRACKER II-CABLE LOCATOR (501)

BURIED FACILITY LOCATION AND MARKING Tracker II

Cat No: 50086626

UPC No: 783310086628

Description

- Traces the path and determines the depth of wires and metallic pipes on active or dead systems without having to deactivate the system
- Lightweight receiver provides audible and visual indications of signal strength
- Transmitter output and receiver sensitivity are fully adjustable for maximum accuracy
- Transmitter offers three methods of connection: direct, inductive coupler and inductive antenna
- Includes transmitter assembly, receiver assembly, inductive coupler (clamp), built-in inductive antenna, two 8' (2.4m) test leads with heavy-duty alligator clips and durable polyethylene case
- High frequency transmitter provides range up to 4,000' (1,219 m) and depths up to 7' (2 m)
- Receiver is 32 IN long (813 mm)
- Battery operated (eight AA and one 9V battery is included)
- Molded carrying case included
- 1-year limited warranty

Specifications

- Automatic Shut Off : 90 MINT Transmitter And Receiver
- Battery Life :
 - Transmitter - 30 HR Nominal
 - Receiver - 10 HR Nominal
- Construction :
 - Transmitter/Receiver-Powder Coated Aluminum
 - Case-Vacuum Formed Polyethylene
- Dimensions : 33.50 IN X 8.250 IN X 3.750 IN
- Power Requirement :
 - Transmitter - (8) AA batteries
 - Receiver - (1) 9V battery
- Replacement Part : 501T Transmitter, 501R Receiver, IC1 Inductive Clamp, CS16 Transmitter Cord Set, 500CA Case with Antenna
- Transmitter Frequency : 447.5 KHZ
- Transmitter Power : 40 Vp-p (140 MILW) Maximum
- Voltage Protection : 240 VAC/500 VDC
- Weight : 6.700 LB