



GE  
Lighting

13699 - GE Daylight T12

F72T12D/HO 15PK

Product Photo



### GENERAL CHARACTERISTICS

Base Description	Recessed Double Contact
Base Type	Pin/Plug-In
Mercury Content	90 mg
Mercury-Picogram per mean lm hr	1612.9
Starting Temp (MIN) C-degrees	-29 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	12000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	R17d
Bulb Shape	T12

### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	4650 lm
Nominal Initial Lumen per Watt	63
Initial Lumens-nominal	5350 lm
Color Rendering Index-CRI	75
Color Temperature	6500 K

### PRODUCT INFORMATION

Product Code	13699
Description	F72T12D/HO 15PK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168136990
Standard Package GTIN	10043168136997
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168136990
Alternative Unit Of Measure	EACH
Standard Package Quantity	15
Ean UPC	043168136990
Standard Package GTIN	00043168136990
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	15
Sales Unit	Each
UCC	043168136990

### DIMENSIONS

Bulb Diameter (DIA) <Max>	1.59 in
Bulb Diameter (DIA) <Min>	1.41 in
Diameter	1.5 in
End of Base Pin to Pin	69.72 in
Nominal Length	72.0 in

### ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	395.00 V @ 10 °C
420.00 V @ -29 °C	Cathode Resistance Ratio - Rh/Rc (MIN)
4.250	Cathode Resistance Ratio - Rh/Rc (MAX)
6.500	Rated power (Watts)

### CAUTIONS & WARNINGS


#### Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

#### Warning

- Risk of Electric Shock

Turn power off before inspection  
installation or removal.



Jan 6, 2017 10:53:01 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)