



Representative Image

## Catalog No. SEHA36AT0060

Description: SEH 3P 600V 60A

UPC No 783164211436

Products > Circuit Breakers > Molded Case Circuit Breakers > Spectra RMS™ Electronic Trip

Spectra RMS Molded Case Circuit Breakers (SE150, SF250, SG600 and SK1200) have a digital, solid state, RMS sensing trip system with field installable, front-mounted rating plugs to establish or change the breaker ampere rating. Adjustable instantaneous with tracking short-time is standard on all frames. The trip system uses digital sampling to determine the RMS value of sinusoidal and non-sinusoidal currents.

### Descriptors

Category	Spectra RMS™ Electronic Trip
GO Schedule	ES

### Specifications

Product Line	Spectra RMS - Standard
Trip Style	Interchangeable
Frame Type	SE150
Amperage	40 A, 50 A, 60 A, 35 A, 45 A
Poles	3
System Voltage	120 Vac, 120/240 Vac, 240 Vac, 277 Vac, 480 Vac, 600 Vac
120 Vac Interrupting Rating	65 KAIC
120/240 Vac Interrupting Rating	65 KAIC
240 Vac Interrupting Rating	65 KAIC
277 Vac Interrupting Rating	25 KAIC
480 Vac Interrupting Rating	25 KAIC
600 Vac Interrupting Rating	18 KAIC
Trip Function	LSI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TCAL18
Long Time	Fixed
Short Time	Adjustable
Instantaneous	Adjustable
Current Metering	No
Protective Relays	No
Special Markings	HACR, HID
GSA Compliance	No

### Classifications

UL File #	E11592
CSA File#	LR40350

## Publications

Title	Publication No.	Publication Type
<a href="#">Spectra RMS MCCB, Type SE150 Plug-in Base, Model</a> Full Scale solid model in .stp format for SE150 3P Plug-in Base.	SE-Plug-in-STP	Drawings-Outline and Dimensional
<a href="#">Spectra RMS MCCB, Type SE150, Model</a> Full Scale solid model in .stp format for SE150 Circuit Breakers.	GEM-2877-STP	Drawings-Outline and Dimensional
<a href="#">Spectra RMS MCCB, Type SE150, Drawing</a> 1-Page, Fully dimensioned outline drawing in .dxf format. Includes door cut-out.	GEM-2877-DXF	Drawings-Outline and Dimensional
<a href="#">SE (60AF 60RP); Long/Tracking Short Time Instantaneous</a> 1-page time current curve.	K215-168B	Time Current Curves
<a href="#">SE (60AF); Let-Through Energy</a> 1-page peak let through energy curve.	K215-203A	Time Current Curves
<a href="#">SE (60AF); Peak Let-Through Current</a> 1-page peak let through current curve.	K215-202A	Time Current Curves
<a href="#">SE (60AF 35/40/45/50RP); Long/Tracking Short Time Instantaneous</a> 1-page time current curve.	K215-167C	Time Current Curves

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.