



VT SERIES


VT Series is designed for heavy duty service in areas subjected to moisture and chemicals. Ideally suited for food processing areas also.



Dimensional Data



Mounting Bracket Optional



Specifications

Mounting: Units may be either surface or pendant mounted. Housing provided with adequate amount of knockouts which must be drilled on job site to insure proper setting.

Construction: One piece housing molded from ABS material with a smooth white exterior. ABS cam-lock latches provide both a positive lock between lens and housing and self hinging for lamp replacement. A self adhesive, closed cell polyethylene gasket on housing forms a continuous seal with diffuser. Internal metal is die-formed from heavy gauge cold rolled steel.

Diffuser: Lens is crepe acrylic.

Wiring: Standard ballast are 120 volt and T5 are Univolt (UV). All 800MA are low temperature (-20°F).

Approval: All units are UL listed.

Ordering Information

<i>Catalog #</i>	<i>Lamp</i>	<i>Length</i>	<i>Catalog #</i>	<i>Lamp</i>	<i>Length</i>
ELECTRONIC T5			ELECTRONIC OCTRON T8		
VT224T5HO/UV	2-F24T5HO	2'	VT120EBO	1-F17T8	2'
VT228T5/UV	2-F28T5	4'	VT220EBO	2-F17T8	2'
VT154HO/UV	1-F54T5HO	4'	VT140EBO	1-F32T8	4'
VT254HO/UV	2-F54T5HO	4'	VT240EBO	2-F32T8	4'
VT154THO/UV	2-F54T5HO	8'	VT340EBO/SP	3-F32T8	4'
VT254THO/UV	4-F54T5HO	8'	VT240TEBO	4-F32T8	8'
ELECTRONIC T12			VT196EBO	1-F96T8	8'
VT148HOEB	1-F48T12HO	4'	VT296EBO	2-F96T8	8'
VT248HOEB	2-F48T12HO	4'	VT248HOEBO	2-F48T8HO	4'
VT196HOEB	1-F96T12HO	8'	VT296HOEBO	2-F96T8HO	8'
VT296HOEB	2-F96T12HO	8'			

Consult factory for other options




VT SERIES

Options and Accessories *Add Suffix*

DIM	Dimming Ballast	UV	Universal Voltage
EM	Emergency Ballast (1 lamp)	REF	Internal Polished Aluminium Reflector
EM/2	Emergency Ballast (2 lamp)	REFS	Internal Specular Silver Reflector
LEX	Polycarbonate Lens	SSL	Stainless Steel Latches
BRK	Mounting Bracket	SSLTP	Stainless Steel Latches Tamper Proof
RFI	Radio Interference Filter	WL	Wet Location Rating
FS	External Fuse Holder		

Installation Data



Photometrics

Photometric Information available upon request.

