

IEC Pin and Sleeve

125A, 220/380V,240/415V, 4 Pole, 5 Wire

Watertight Receptacle

Features

- Corrosion-resistant self-closing gasketed cover
- Sequential contact engagement to prevent a momentary over-voltage on components
- Super tough insulated non metallic house for impact and chemical resistance
- Super tough insulated non-metallic housing
- Multi contact spring provides and maintains high unit pressure on mating pins to minimize temperature rise

Ordering Information

Description	UPC	Catalog Number
Watertight IEC Pin and Sleeve Receptacle	783585405162	HBL5125R6W
Device Color		
Red		

Standards

Listed to standard UL1682
CSA StandardC22.2 No. 182.1
UL Listed, File E146032

Specifications

Housing	Zytel® 101 Nylon
Mounting Flange	Zytel® 101 Nylon
Cover	Reinforced Thermoplastic Polyester
Gaskets	Solid Neoprene
Cover Screw	Nickel-plated brass

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V RMS
Temperature Rise	Max. 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%

Mechanical

Impact Resistance	Per CSA C22.2 No.182.1 /UL1682
Product Identification	Identification and ratings are a permanent part of the device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions

Environmental

Flammability	HB or better per UL 94 or CSA C22.2 No. 0.17
Ingress Protection	IP67 Suitability
Moisture Resistance	Watertight per IEC 60309-1
Operating Temperatures	Maximum Continuous 75°C; Minimum - 40°C w/o impact

Accessories

- Back Boxes
- Cover Assemblies

Online Resources

- Customer Use Drawing
- eCatalog
- Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

HUBBELL

