

DATE:	TYPE:	
NAME:		
PROJECT:		

Compact fluorescent

P5806-09

Valera

Two-light energy efficient CFL Linear Lantern finished in Brushed Nickel.

Category: Outdoor

Finish: Brushed Nickel (plated)

Construction: Die-cast aluminum construction

Glass: White polycarbonate diffuser



Width: 5-5/8" Height: 16-1/8" Depth: 4" H/CTR: 8"

Glass: 5-3/8" W. Length: 16" Height: 3-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included covers a standard 4" hexagonal recessed outlet box	Pre-wired 6" of wire supplied 120V	Quantity: 2 18W GU-24 GU24 plastic sockets	cCSAus Wet location listed 1 year warranty Companion fixtures are available Title 24 compliant