

Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshow s | Support

United States > Energy > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Electrical Tape, Mastics & Special Use > Rubber Tapes - Insulating and Splicing > 3M™ Temflex™ Rubber Splicing Tape 2155

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Temflex™ Rubber Splicing Tape 2155



- Print

3M™ Temflex™ Rubber Splicing Tape 2155 is a conformable self-fusing rubber electrical insulating tape. It is designed for low voltage electrical insulating and moisture sealing applications. Compatible with solid dielectric cable insulations.

-

Need Help?

Questions? We can help [Contact Us](#)

Overview	Documents																																								
Specifications <table><tr><td>Adhesive Material</td><td>Rubber Resin</td></tr><tr><td>Agency Approvals</td><td>UL Listed, File E129200, UL Listed</td></tr><tr><td>Backing Material</td><td>Rubber</td></tr><tr><td>Backing Thickness (metric)</td><td>76 mm</td></tr><tr><td>Brand</td><td>Temflex™</td></tr><tr><td>Breaking Strength</td><td>157 N/cm</td></tr><tr><td>Color</td><td>Black</td></tr><tr><td>Dielectric Strength (V/mil)</td><td>600</td></tr><tr><td>Elongation</td><td>700 %</td></tr><tr><td>Elongation at Break</td><td>700%</td></tr><tr><td>Family</td><td>3M™ Temflex™ Rubber Splicing Tape 2155</td></tr><tr><td>Length</td><td>22 Linear Foot</td></tr><tr><td>Length (Metric)</td><td>6.7 m</td></tr><tr><td>Liner/Linerless</td><td>Liner</td></tr><tr><td>Maximum Operating Temperature (Celsius)</td><td>80 Degree Celsius</td></tr><tr><td>Operating Temperature (Fahrenheit)</td><td>Up to 176 Degree Fahrenheit</td></tr><tr><td>Product Family</td><td>3M™ Temflex™ Rubber Splicing Tape 2155</td></tr><tr><td>Product Type</td><td>Rubber Tapes</td></tr><tr><td>RoHS 2011/65/EU Compliant</td><td>Yes</td></tr><tr><td>RoHS EU Comments</td><td>RoHS 2011/65/EU compliant without exemption *Important RoHS information</td></tr></table>		Adhesive Material	Rubber Resin	Agency Approvals	UL Listed, File E129200, UL Listed	Backing Material	Rubber	Backing Thickness (metric)	76 mm	Brand	Temflex™	Breaking Strength	157 N/cm	Color	Black	Dielectric Strength (V/mil)	600	Elongation	700 %	Elongation at Break	700%	Family	3M™ Temflex™ Rubber Splicing Tape 2155	Length	22 Linear Foot	Length (Metric)	6.7 m	Liner/Linerless	Liner	Maximum Operating Temperature (Celsius)	80 Degree Celsius	Operating Temperature (Fahrenheit)	Up to 176 Degree Fahrenheit	Product Family	3M™ Temflex™ Rubber Splicing Tape 2155	Product Type	Rubber Tapes	RoHS 2011/65/EU Compliant	Yes	RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Adhesive Material	Rubber Resin																																								
Agency Approvals	UL Listed, File E129200, UL Listed																																								
Backing Material	Rubber																																								
Backing Thickness (metric)	76 mm																																								
Brand	Temflex™																																								
Breaking Strength	157 N/cm																																								
Color	Black																																								
Dielectric Strength (V/mil)	600																																								
Elongation	700 %																																								
Elongation at Break	700%																																								
Family	3M™ Temflex™ Rubber Splicing Tape 2155																																								
Length	22 Linear Foot																																								
Length (Metric)	6.7 m																																								
Liner/Linerless	Liner																																								
Maximum Operating Temperature (Celsius)	80 Degree Celsius																																								
Operating Temperature (Fahrenheit)	Up to 176 Degree Fahrenheit																																								
Product Family	3M™ Temflex™ Rubber Splicing Tape 2155																																								
Product Type	Rubber Tapes																																								
RoHS 2011/65/EU Compliant	Yes																																								
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information																																								

Self-Extinguishing	No
Self Sticking/Amalgamating	Yes
Shelf Life	3 Year
Suitable for High Voltage	No
Tape Color	Black
Tape Grade	General Use
Tape Length (metric)	6.7 m
Tape Type	Rubber Insulating and Splicing
Tensile Strength	300 Pound-Force Per Square Inch
Tensile Strength lb/in (N/100 mm)	9 (158)
Thickness	30 mil
Thickness (Metric)	0.76 mm
Trademark	Temflex
UL File Number	E129200
UV Resistant	No
Voltage Rating	600 V
Vulcanizing	Yes
Width	0.75 Inch
Width (Metric)	19 mm