

DATA -VOICE CABLE

Cat5e -Enhanced Category 5E UTP
PVC/CMR/MPR
350 MHz



CONSTRUCTION

Conductor	- Solid annealed Bare copper
Insulation	- PVC: polyolefin
Jacket	- PVC: flame retardant PVC (Polyvinyl Chloride)

Applications:

- 4 Mbps Token Ring (IEEE 802.5)
- 10 Mbps 10 BASE-T ETHERNET (IEEE 802.3)
- 16 Mbps Token Ring (IEEE 802.5)
- 100 Mbps (ANSI X3T9.5 TPDDI)
- 100 VG ANYLAN (IEEE 802.12)
- 100Mbps 100 BASE-T Fast ETHERNET (IEEE 802.3)
- 155 Mbps ATM
- 622 Mbps ATM
- 1000 Mbps 1000 BASE-T Gigabit ETHERNET (IEEE 802.3)

Standards:

- ANSI/TIA/EIA 568-A
- FCC PART 68
- ETL/UL Available

Part #	AWG	Pairs	Nom. O.D.	Lbs./M'
J462404	24	4	.197"	20

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.