

Product data sheet

Characteristics

500SV1B

XFMR DRY 1PH .5KVA 240X480V-120/240V

Product availability : Stock - Normally stocked in distribution facility



Price* : 386.00 USD



Main

Product or component type	Dry Sealed Transformer
Primary voltage	240 x 480 V
Secondary voltage	120/240 V
Number of tap-offs	0

Complementary

Box number	5A
Phase	1 phase
Primary voltage	240 x 480 V : 120/240 V
Rated power in VA	0.5 kVA
Temperature rise	80 °C
Height	5.5 in
Width	6.19 in
Depth	4.69 in
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel

Environment

NEMA degree of protection	NEMA 3R
Insulation temperature	266 °F (130 °C)
Product certifications	CSA cULus UL listed

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2

GTIN	00785901019831
Nbr. of units in pkg.	1
Package weight(Lbs)	15.25
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------