



# Standard

## STANDARD VH1B13TPWI

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

### Product data

General Information	
Lamp Type	CFQ13W/GX23
Number Of Lamps	1 piece/unit
Lamp Footage	-
Ballast Type	Magnetic Fluorescent
Base Model	VH1B13TPW
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	277 V
Input Frequency	60 Hz
Total Harmonic Distortion USA	30 %
Ignition Method	Preheat
Crestfactor (Nom)	1.5
Ignition Time (Nom)	1 s
Input Current (Open Circuit)	0.26
Input Current (Starting)	0.3
Ballast Factor (Nom)	0.99
Power Factor (Nom)	0.88
Input Current (Nom)	0.1 A
Input Power (Nom)	24 W

Rated Lamp Power	13 W
------------------	------

Wiring	
Wire Striplength	0.50/0.375 mm
Lamp Connection	Series
Wire Length By Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Max Ballast-Lamp Distance Remote Wiring	30'
Max Ballast-Lamp Distance Tandem Wiring	-
Max Ballast-Lamp Distance Through Wiring	-

Mechanical and Housing	
Housing Material	Metal
Housing	R2
Housing Dimensions	4.75" x 2.22" x 1.63"


Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant

## Standard

Hum And Noise Level	A
UL Recognized	No
<b>Product Data</b>	
Order product name	STANDARD VH1B13TPWI
EAN/UPC - Product	781087043486
Order code	913700517819

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700517819
Net Weight (Piece)	0.613 kg

### Dimensional drawing



Product	A1	A2	B1	C1
STANDARD VH1B13TPWI	4.75 in	4.38 in	2.22 in	1.63 in

MAG BALLAST (1) 13W COMPACT(2-PIN) 277V

