

Product availability : Stock - Normally stocked in distribution facility



Price* : 26.30 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	Homeline
Line Rated Current	20 A
Product certifications	UL listed
System Voltage	120 V AC
Mounting mode	Plug-in
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated
Electrical connection	Clamp terminal for 2 cables
AWG gauge	AWG 14...AWG 8 for 1 x aluminium/copper AWG 14...AWG 10 for 2 x copper

Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901065210
Nbr. of units in pkg.	10
Package weight(Lbs)	0.28000000000000003
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	Lifetime
-----------------	----------