


# NTM-713 Aluminum Baffle Cone with White Flange

## TRIM DIMENSIONS



Trim OD: 7-1/4"  
Aperture: 5-3/4"  
Height: 5-1/4"

## FEATURES

### Trim

Precision spun 0.040 aluminum baffle with deep grooves to reduce aperture glare and white flange.

### Mounting

Trim includes two "V" torsion springs to mount trim securely to housing. Replacement "V" torsion springs are available (NRA-86). Socket can be mounted directly to trim without bracket.

### Compatible Housings

NTM-713 is compatible with Line Voltage housings.  
See individual specification sheets for more information.

### Lamp

#### Line Voltage

100W BR40/PAR38 Maximum (NHIC-17QAT; NHIC-17QNBAT; NHIC-17/100DWQA;  
NHR-26Q; NHRIC-17QAT; NHRIC-17QNBAT)

150W BR40/PAR38 Maximum (NH-26Q; NH-26QNB; NHR-26Q)

### Labels and Listings

cULus Listed for Damp Location when used with compatible housing

## Aluminum Baffle Cone with White Flange

**NTM-713BAL:** Black Aluminum Baffle Cone with White Flange

**NTM-713WAL:** White Aluminum Baffle Cone with White Flange

Type


Project

Catalog No.


Lamp/Wattage

## HOUSING DIMENSIONS


NH-26Q / NH-26QNB / NHIC-17QAT / NHIC-17QNBAT



NHIC-17/100DWQA



NHR-26Q / NHRIC-17QAT / NHRIC-17QNBAT



## Compatible Housings

### LINE VOLTAGE

Item Number	Installation Type	Lamp	Dimensions
NH-26Q	Non-IC New Construction	150W Max.	W: 7" L: 10-1/8" H: 7-1/2"
NH-26QNB	Non-IC New Construction	150W Max.	W: 7" L: 10-1/8" H: 7-1/2"
NHIC-17/100DWQA	IC Double Wall Air-Tight NC	100W Max.	W: 9-1/8" L: 12-1/2" H: 7-3/4"
NHIC-17QAT	IC Air-Tight New Construction	100W Max.	W: 7" L: 10-1/8" H: 7-1/2"
NHIC-17QNBAT	IC Air-Tight New Construction	100W Max.	W: 7" L: 10-1/8" H: 7-1/2"
NHR-26Q	Non-IC Remodel	150W Max.	W: 6-3/4" L: 13-3/4" H: 7-1/2"
NHRIC-17QAT	IC Air-Tight Remodel	100W Max.	W: 6-3/4" L: 13-3/4" H: 7-1/2"
NHRIC-17QNBAT	IC Air-Tight Remodel	150W Max.	W: 6-3/4" L: 13-3/4" H: 7-1/2"