



Electrical Utility

[Products](#) | [Solutions](#) | [Documentation & Literature](#) | [News & Tradeshow](#)s | [Support](#)

[United States](#) > [Energy](#) > [Electrical Utility](#) > [Products](#) > [Electrical Utility Products Catalog](#) > [Splices](#) > [Low Voltage Splices \(<1 kV\)](#) > [3M™ Heat Shrink Splice Kits](#) > [3M™ Heat Shrink Heavy-Wall Cable Sleeves for 1 kV ITCSN-0800-9-Box, 8-1/0 AWG, Expanded/Recovered I.D. 0.80/0.20 in, 9 in Length, boxed](#)

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Heat Shrink Heavy-W all Cable Sleeves for 1 kV ITCSN-0800-9-Box, 8-1/0 AWG, Expanded/Recovered I.D. 0.80/0.20 in, 9 in Length, boxed

3M ID 80610229496    UPC# 00054007088905    Part Number **ITCSN-0800-9"-Black-25 Pcs**



3M™ ITCSN Heat Shrink Cable Sleeve is a heavy-wall sleeve that provides abrasion, corrosion and chemical resistance. This sleeve has a 3:1 shrink ratio to offer electrical insulation for 1 kV-rated applications. It features a cross-linked polyolefin construction that provides moisture-seal protection.

- Superior resistance to abrasion, corrosion and chemicals
- Offers reliable performance for electrical splices, connections and terminations
- Suitable for insulating secondary splices, as well as direct buried, submersible and dig-in repairs
- Expanded I.D. of 0.8 in
- 9-in piece
- Made of black cross-linked polyolefin
- Withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C)
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- 25 pieces/case

Where to Buy

[Print](#)

Need Help?

Questions? We can help [Contact Us](#)

Overview	Documents
<p>3M™ Heat Shrink Cable Sleeve ITCSN is color-coded for quick and easy identification of the wire. This split-resistant sleeve has a factory-applied adhesive/sealant that offers reliable performance for electrical splices, connections and terminations. It is perfect for insulating secondary splices, direct buried, submersible or dig-in repairs, as well as physical protection of high-voltage, air-insulated connectors or lugs. It withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C). UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.</p>	
<h3>Specifications</h3>	
Brand	3M™
Color	Black
Elongation	4.75 %
Family	3M™ Heat Shrink Heavy-Wall Cable Sleeves ITCSN
Length	9 Inch
Material	Adhesive-lined Polyolefin
Non-Corrosive	Yes
Specifications	UL 486D*
Trademark	3M™
Voltage	1 kV

---

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M Electrical Utility: [Contact Us](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2018. All Rights Reserved.

---