



Photocontrols : Fixed Mount Thermal Photocontrols

K4223C | Stem and Swivel Mount Thermal Photocontrol, 208-277 V



K4223C

STEM AND SWIVEL MOUNT THERMAL PHOTOCONTROL, 208-277 V

These photocontrols are provided with a swivel arm for easy and flexible installation to standard outdoor light fixtures or electrical boxes.



Features & Applications

Features

- Mechanical bimetal switch with Cadmium Sulfide photocell
- Delay feature prevents unwanted OFF switching
- High strength, UV resistant plastic housing
- Swivel with 1/2"-14 NPSM threaded stem
- Washer gasket and locking nut included
- #18 AWG, 6" wire leads

Applications

- Exterior Lighting
- Street Lighting
- Parking Lot
- Pedestrian Pathway
- Landscape Lighting

Specifications

Photocontrol Style	Sensor Time Delay	Operating Temperature Min (F)
Stem, Swivel Mount	30 sec to 90 sec	-40
Photocontrol Sensor Location	Wire Lead Length (in)	Cover Color
Side	9	Gray
Input Voltages Display	Wire Lead Length (mm)	Product Height (mm)
208-277 VAC, 50/60 Hz	228.6	139.7
Inductive	Wire Size Max	Product Width (mm)

This website uses cookies to provide a better user experience.

Accept

3/24/2017	K4223C - Intermatic	
8.3 A, 208-277 VAC, 50/60 Hz	#18 AWG	39.7
Incandescent Load Ratings	Operating Temperature Max (°C)	Product Depth (mm)
15 A, 208-277 VAC, 50/60 Hz	70	39.7
Activation Off	Operating Temperature Max (F)	Warranty
3 to 15 fc	158	2-year limited
Activation On	Operating Temperature Min (°C)	
1 to 5 fc	-40	

Related Accessories and Parts (2)



22LG116

REPLACEMENT LIGHT GUARD FOR THERMAL PHOTOCONTROLS
(K4100 AND K4200 SERIES)

K42-SW-A

SWIVEL ARM

Copyright © 2016 Intermatic Incorporated. All rights reserved.