

Heat-a-Vent

MODEL: 9905

DESCRIPTION

Two functions in one unit. Use them individually or together.

- 1500 watt heating element provides fan forced heat.
- Vent fan exhausts stale air and moisture.
- Streamline design with handsome white grille. Grille is tough polymeric, impervious to bathroom climate.
- Built in junction box with receptacles for simple plug-in installation of heater and fan motor.

SPECIFICATIONS

Electrical Rating: 120V, 60Hz
1620 total watts

Certified air performance: 70 CFM at .1 SP, typical

Certified Sound Level: 4.0 Sones typical

Housing: Dimensions: 14" x 9 $\frac{3}{4}$ " x 7 $\frac{3}{4}$ "H.
Material: Cold rolled steel, enamel finish.

Heating Element: Nickel-Chromium coiled resistance wire.

Thermal Protection: Automatic resetting thermal limit protector.


Motors: Thermally protected, shaded pole, sleeve bearing.

Switch: Separate On/Off wall switch for heat and vent functions.

Exhaust Duct: Snap on polypropylene duct adapter and damper designed for 4" round design.

Installation instructions included with each unit.

Not designed for installation over a tub or in a shower unit.



ARCHITECTS SPECIFICATIONS

Heat-A-Vent shall be model 9905 as manufactured by NuTone according to listed specifications.

CERTIFIED TEST DATA

- Air delivery 70 CFM.
- Sound level: 4.0 sones.

