



Measurements:

<u>Height</u>	<u>Width</u>
16.00"	15.25"
<u>Max OAH</u>	
62.50"	
<u>Hanging Weight</u>	
13.69 lb	

Lamping:

Xenon G9 Xenon	0 Rated Lumens
6.00 40W G9 Xenon	Color Temperature
240 total watt	2,000 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
20.12 lb	18.50"	16.00"	18.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209008397	Yes	

Finish:

Polished Nickel PN

Glass:

Water Glass WG

Material:

Steel

Certification:

Dry Location

Additional:

G9 Xenon (Included)
Slope: 120