




20 AMP POWER CONTROL RELAYS


RIB2401SB

Enclosed Relay 20 Amp SPST-N/O + Override with 24 Vac/dc/120 Vac Coil



RIB2402SB

Enclosed Relay 20 Amp SPST-N/O + Override with 24 Vac/dc/208-277 Vac Coil





SPECIFICATIONS

Relays & Contact Type: One (1) SPST Continuous Duty Coil Expected Relay Life: 10 million cycles minimum mechanical

Operating Temperature: -30 to 140° F

Humidity Range: 5 to 95% (noncondensing)

Operate Time: 18ms

Relay Status: LED On = Activated

Dimensions: 2.30" x 3.20" x 1.80" with .50" NPT Nipple Wires: 16", 600V Rated

Approvals: UL Listed, UL916, UL864, UL508, C-UL

California State Fire Marshal, CE, RoHS

Housing Rating: UL Accepted for Use in Plenum, NEMA 1

Gold Flash: No Override Switch: Yes

Contact Ratings:

20 Amp Resistive @ 277 Vac
20 Amp Ballast @ 277 Vac (N/O)
10 Amp Ballast @ 277 Vac (N/C)
Not rated for Electronic Ballast
10 Amp Tungsten @ 120 Vac (N/O)
770 VA Pilot Duty @ 120 Vac
1,110 VA Pilot Duty @ 277 Vac
2 HP @ 277 Vac

1 HP @ 120 Vac

Coil Voltage Input:

24 Vac/dc; 120 Vac; 50-60 Hz (RIB2401SB) 24 Vac/dc; 208-277 Vac; 50-60 Hz (RIB2402SB)

Drop Out = 2.1 Vac / 3.8 Vdc Pull In = 18 Vac / 22 Vdc

Coil Current:

50 mA @ 18 Vac 33 mA @ 22 Vdc 83 mA @ 24 Vac 35 mA @ 24 Vdc 47 mA @ 120 Vac (RIB2401SB) 47 mA @ 30 Vdc 69 mA @ 208-277 Vac (RIB2402SB)

Notes:

• Order Normally Closed by adding "-NC" to end of model number