



GE  
Lighting

## 68171 - GE LED Globes

### LED4DG25M-W/TP

- GE LEDs offer outstanding energy efficiency, long-lasting performance and just-right brightness, all in one package. They're dimmable and illuminate your home with soft, warm light. Use this GE LED decorative globe bulb in pendant lights and vanity light fixtures. Its spherical shape provides a finishing touch to your fixtures. It's great for frequently used fixtures—GE LED's long life and low energy use will help you save money on energy.
- 25 watt replacement using only 4.5 watts
- Lasts 13.7 years based on 3 hours per day usage
- Estimated yearly energy costs \$0.54 based on 3 hours per day \$0.11 per kWh
- \$33 in energy savings over the life of the bulb based on 3 hours per day usage
- 2700K-soft white color appearance
- G25 globe shape with medium base for vanity strip and pendant light fixtures

### Product Photo



## GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	Globe
Primary Application	Globe
Product Technology	LED
Rated Life (Hours)	15000 h
10 Digit U	4316868171
Lamp Count	1
Life in Years	13.7 yr
Replacement Watts	25 W
Requested Structure	Blister - Carded, Tray Pack
Estimated Energy Cost per Year	0.54
Base	E26
Bulb Shape	G25

## PHOTOMETRIC CHARACTERISTICS

Lumens per Watt (Efficacy)	62 lm
Nominal Initial Lumen per Watt	62
Initial Lumens-nominal	280 lm
Color Rendering Index-CRI	82
Color Temperature	2700 K

## PRODUCT INFORMATION

Product Code	68171
Description	LED4DG25M-W/TP
Alternative Unit Of Measure	EACH
Standard Package Quantity	3
Ean UPC	043168681711
Standard Package GTIN	00043168681711
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	3
Sales Unit	Each
UCC	043168681711
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168681711
Standard Package GTIN	10043168681718
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168681711

## DIMENSIONS

Bulb Max Overall Length-MOL	4.3 in
-----------------------------	--------

## ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	4.5 W

## CAUTIONS & WARNINGS

### Caution

Risk of Electric Shock

Suitable for damp locations

Not for use totally enclosed luminaires.

Not intended for use with emergency exit fixtures or emergency exit lights.