



Measurements:

<u>Height</u>	<u>Width</u>
6.00"	15.50"
<u>Hanging Weight</u>	
3.37 lb	

Lamping:

Incandescent MB Incandescent	2,016 Rated Lumens
3.00 60W MB Incandescent	Color Temperature
180 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
4.74 lb	16.10"	6.30"	16.10"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209056633	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)