




### P2260 THRU P2270

Wt/100 pcs: 78 Lbs (35.4 kg)



Part Number	"A" Degree (rad)	"B" In (mm)
P2270	82 1/2° 1.44	3 5/8 91
P2269	75° 1.31	3 5/8 91
P2268	67 1/2° 1.18	3 5/8 91
P2267	60° 1.05	3 11/16 94
P2266	52 1/2° 0.92	3 11/16 94
P2265	45° 0.79	3 11/16 94
P2264	37 1/2° 0.65	3 11/16 94
P2263	30° 0.52	3 11/16 94
P2262	22 1/2° 0.39	3 3/4 95
P2261	15° 0.26	3 3/4 95
P2260	7 1/2° 0.13	3 3/4 95

**Standard Dimensions for 1 5/8" (41mm) width series channel fittings (Unless Otherwise Shown on Drawing)**

Hole Diameter: 9/16" (14mm); Hole Spacing - From End: 13/16" (21mm); Hole Spacing - On Center: 1 7/8" (48mm); Width: 1 5/8" (41mm); Thickness: 1/4" (6mm)

### MATERIAL

Fittings, unless noted, are made from hot-rolled, pickled and oiled steel plates, strip or coil, and conform to ASTM specifications A575, A576, A635, or A36. The fitting steel also meets the physical requirements of ASTM A1011 SS GR 33. The pickling of the steel produces a smooth surface free from scale.

Many fittings are also available in stainless steel, aluminum and fiberglass. Consult factory for ordering information.

### FINISHES

Fittings are available in:

Perma-Green III (GR),

Electro-galvanized (EG), conforming to ASTM B633 Type III SC1;

Hot-dipped galvanized (HG), conforming to ASTM A123 or A153 and

Plain (PL).

Project: \_\_\_\_\_

Architect / Engineer: \_\_\_\_\_

Date: \_\_\_\_\_ Phone: \_\_\_\_\_

Contractor: \_\_\_\_\_

Address: \_\_\_\_\_

Notes 1: \_\_\_\_\_

Notes 2: \_\_\_\_\_

**Approval Stamp:**