

DESCRIPTION

The CSWEU2 is a wet location listed emergency lighting unit made of injection molded, flame retardant thermoplastic with grey finish with a high-impact, fully-gasketed poly-carbonate shield. The integral heads are fully adjustable and contain 2 6VDC, 7 watt halogen lamps.

MOUNTING

The back housing contains a molded-in template for wall mounting to any standard universal J-Box. Front cover is secured with 2 gasketed screws.

APPLICATION

The CSWEU2 can be applied in areas that are susceptible to rain and severe moisture, such as parking decks and outdoor commercial applications.

COMPLIANCES

UL924
UL Wet Location Listed



ELECTRICAL/BATTERY

- Dual voltage input 120/277VAC, 60 Hz
- AC Lock-out feature prevents battery dis-charge until unit is energized
- Maintenance-free 6VDC, 4.5Ah lead calcium battery
- Low voltage battery disconnect prevents deep dis-charge
- UL924 listed for wet applications (10°C to 40°C)
- Fully automatic, solid state charger
- AC-on indicator and Push-to-Test switch

Photometric files are available on the Compass website.

ORDERING GUIDE

Catalog Number	Description	Voltage	Lamp Watts (Each)
CSWEU2	Wet Location Emergency Light with MR-16 Halogen Adjustable Lamps and Poly-Carbonate face-shield	6 VDC	7 Watts

DIMENSIONS

