

8471 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacketed Con



For more Information
please call

1-800-Belden1

**General Description:**

16 AWG stranded (19x29) tinned copper conductors, PVC insulation, twisted pair, PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	16	19x29	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.023

Inner Shield

Inner Shield Material:

Inner Shield Material
Unshielded

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.032

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Direction	Twists (twist/ft)
2.000	Left Hand	6.000

Overall Nominal Diameter: 0.274 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & White

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
Non-UL Temperature Rating:	60°C (UL AWM Style 2598)
Bulk Cable Weight:	36 lbs/1000 ft.
Max. Recommended Pulling Tension:	61 lbs.
Min. Bend Radius/Minor Axis:	2.750 in.

8471 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacketed Con

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL3, CMG
-------------------------	----------

NEC Articles:	800, 725
---------------	----------

CEC/C(UL) Specification:	CMG
--------------------------	-----

AWM Specification:	UL Style 2598 (300 V 60°C)
--------------------	----------------------------

EU Directive 2011/65/EU (ROHS II):	Yes
------------------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 FT4 Loading
----------------	--------------------

CSA Flame Test:	FT4
-----------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/ft)

0.190

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

33

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.49

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Description	Current
10C temperature rise	6.1 Amps per conductor @ 25°C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8471 060U1000	1,000 FT	38.000 LB	CHROME		1 PR #16 PVC FRPVC
8471 060U500	500 FT	20.500 LB	CHROME		1 PR #16 PVC FRPVC
8471 0601000	1,000 FT	40.000 LB	CHROME	C	1 PR #16 PVC FRPVC
8471 060500	500 FT	20.000 LB	CHROME	C	1 PR #16 PVC FRPVC
8471 0605000	5,000 FT	195.000 LB	CHROME		1 PR #16 PVC FRPVC

Notes:

8471 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacketed Con

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-02-2013

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).