



# T5 Standard

## F28T5/841 ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

### Product data

General Information	
Cap-Base	G5 [ G5]
Bulb Shape	T5 [ 16 mm (T5)]
Life To 50% Failures Preheat (Nom)	24000 h
Features	HE Alto® [ High Efficiency Alto]
System Description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Initial lumen (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2625 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
Chromaticity Coordinate X (Nom)	380
Chromaticity Coordinate Y (Nom)	380
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color Rendering Index (Max)	85

Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Rated) (Nom)	27.9 W
Lamp Current (Nom)	0.170 A

### Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Cap-Base Information	Green [ Green Cap]
----------------------	--------------------

## T5 Standard

### Approval and Application


Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg

### Product Data

Order product name	28W/841 Min Bipin T5 HE ALTO UNP/40
EAN/UPC - Product	046677230869
Order code	230862

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927990684022
Net Weight (Piece)	104.500 g
ILCOS Code	FDH-28/40/1B-L/P-G5-16/1150

### Dimensional drawing



TL5 HE F28T5/841 HE Alto

Product	D	A	B	B	C
28W/841 Min Bipin T5 HE ALTO UNP/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

