



# MR16 LED

7MR16/END/F24 2700 DIM10/1

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatibility allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

## Product data

### • General Characteristics

Cap-Base	GU5.3
Bulb	MR16 [MR 16inch/50mm]
Rated Avg. Life (Hours)	40000 hr

### • Light Technical Characteristics

Color Code	WW
Color Designation	Warm White
Beam Angle	24 D
Beam Description	- [-]
Correlated Color Temperature	2700 K
Approx. MBCP	1470 cd
CRI	82
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	360 Lm

### • Electrical Characteristics

Wattage	7 W
Wattage Technical	7.0 W
Voltage	12 V

Line Frequency	50-60 Hz
Power Factor	0.8 -
Lamp Current mA	650 mA
Dimmable	Yes

### • Product Dimensions

Overall Length C	53.7 mm
Overall Length C [inch]	2.116 (max) in
Diameter D	50 mm

### • Product Data



Product number	414680
Full product name	7MR16/END/F24 2700 DIM10/1
Short product name	7MR16/END/F24 2700 DM10/1
Pieces per Sku	1
eop_pck_cfg	10
Skus/Case	10
Bar code on pack	46677414689
Bar code on case	50046677414684
Logistics code(s)	929000179002
eop_net_weight_pp	0.035 kg

## Dimensional drawing



**PHILIPS**  
sense and simplicity

## Dimensional drawing



GU5.3

### 7MR16/END/F24 2700 DIM10/1

Product	C (Norm)	D (Norm)
LED 7W GU5.3 2700K 12V MR16 24D Dimm	53.7	50



© 2013 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2013, January 16  
data subject to change