CR Series

CR24[™] 2' x 4' Architectural LED Troffer

Product Description

The CR24™ architectural LED troffer delivers up to 130 lumens per watt of exceptional 90 CRI light at 4000 lumens. This breakthrough performance is achieved by combining the high efficacy and highquality light of Cree TrueWhite® Technology with a unique thermal management design. Its design makes the CR24 perfect for use in commercial new construction or renovated spaces. The CR24 product family is available in warm, neutral, cool, or daylight color temperatures and has step, 0-10V, or Lutron EcoSystem[®] Enabled dimming options.

Performance Summary

Utilizes Cree TrueWhite® Technology (90 CRI)

Room-Side Heat Sink

Efficacy: 90-130 LPW

Initial Delivered Lumens: 2,200, 3,100, 4,000, 5,000 lumens

Input Power: 22-50 watts

CRI: 90 CRI (Cree TrueWhite® Technology), 80+ CRI

CCT: 3000K, 3500K, 4000K, 5000K

Input Voltage: 120-277 VAC or 347 VAC*

Limited Warranty*: 10 years

Limited Warranty Emergency Back Up (EB) Battery: 1 Year Battery Back Up. Test regularly in accordance with local codes

Controls: Step Level to 50%, 0-10V Dimming or Lutron EcoSystem Enabled to 5%¹

Mounting: Recessed*

*See http://lighting.cree.com/warranty for warranty terms * Acceptable for use with standard 9/16 T-Bar or larger when installed per installation instructions. Consult factory for non-standard grid applications

Accessories


Field-Installed

Adjustable Cable AC5 72 PD8 JB AC5 18/4 72 PD8 JB Chicago Plenum Field Kit CPLCR **Chicago Plenum Field Kit-Emergency** CPLCR EM

Junction Box EJBCR 5PK Expanded size junction box for through wiring (5 pack) Power Whip PW 18/4 06 9T/SS CR

347 Volt CR 347V Step Dimming to 50% CR 347V SD Surface Mount Kit SMK CR24





NOTE: Use of Expanded Junction Box will expand the depth to 6.67" and Emergency Backup will expand the depth to 6.30". Use of 347V will increase fixture height by 1.4"

Ordering Information Example: CR24-40L-40K-10V

CR24					
Product	Initial Delivered Lumens	ССТ	Voltage	Control	Options
CR24	22L ¹ 22W, 2200 lumens - 100 LPW - Only available in 35K or 40K options 31L ¹ 34W 3100 lumens - 90 LPW 40L 40W 4000 lumens - 100 LPW 40LHE ¹ 30.5W 4000 lumens - 130 LPW (30K) 32W 4000 lumens - 120 LPW (30K) 33W 4000 lumens - 120 LPW (40K) 34.5W 4000 lumens - 115 LPW (50K) 50L ² 50W 5000 lumens - 100 LPW	30K 3000K 35K 3500K 40K 4000K 50K 5000K	Blank 120-277 Volt 347 Volt - Integrated option available on 40L only. Other types require addition of a 347 accessory kit (see table above)	S Step Dimming to 50% 10V 0-10V Dimming to 5% LES ³ Lutron EcoSystem® Enabled to 5%	HD CRI 80+ (44W 4000 lumens - 90 LPW) - Available only with 40L EB14 ⁴⁵ Emergency Backup - 1400 lumens - Not for use with SMK Kits. Use EB14SMK EB14SMK ⁴⁵ Emergency Backup with surface mount kit - 1400 lumens - Includes surface mount kit accessory (SMK-CR14)

1. Not available with HD 2. Not available with HD, EB14, EB14SMK 3. Not available in the following options: 22L: 30K or 50K; 31L: All Colors; 40LHE: All Colors 4. Not available in 50L 5. Not available in LES types except 40L LES type

NOTE: Price adder may apply depending on configuration

C V







Rev. Date: V4B 12/22/2016



Canada: www.cree.com/canada

T (800) 473-1234 F (800) 890-7507

Product Specifications

CREE TRUEWHITE® TECHNOLOGY

A revolutionary way to generate high-quality white light, Cree TrueWhite® Technology is a patented approach that delivers an exclusive combination of 90+ CRI, beautiful light characteristics, and lifelong color consistency, all while maintaining high luminous efficacy – a true no compromise solution

CREE LED TECHNOLOGY

Cree's total systems approach to product development is a comprehensive engineering philosophy that combines the most advanced LED sources, driver technologies, optics and forms. The result is highly-reliable luminaire solutions for both indoor and outdoor applications that reduce energy use, extend lifetimes, and maximize illumination performance and quality.

ROOM-SIDE HEAT SINK

An innovative thermal management system designed to maximize cooling effectiveness by integrating a unique room-side heat sink into the diffusing lens. This breakthrough design creates a pleasing architectural aesthetic while conducting heat away from LEDs in a temperature-controlled environment. This enables the LEDs to consistently run cooler, providing significant boosts to lifetime, efficacy, and color consistency.

CONSTRUCTION & MATERIALS

- Durable 22-gauge steel housing with standard troffer access plate for electrical installation
- One-piece lower reflector finished with a textured high reflectance white polyester powder coating creates a comfortable visual transition from the lens to the ceiling plane
- Includes t-bar clips and holes for mounting support wires enable recessed or
- suspended installation
- Individual luminaires may be mounted end to end for a continuous row of illumination

OPTICAL SYSTEM

- Unique combination of reflective and refractive optical components achieves a uniform, comfortable appearance while eliminating pixelation and color fringing
- Components work together to optimize distribution, balancing the delivery of high illuminance levels on horizontal surfaces with an ideal amount of light on walls and vertical surfaces. This increases the perception of spaciousness
- Diffusing lens integrated with upward-facing LED strip eliminates direct view of LEDs while lower reflector balances brightness of lens with the ceiling to create a low-glare high angle appearance

ELECTRICAL SYSTEM

- Integral, high-efficiency driver
- Power Factor: = 0.9 nominal
- Input Power: Stays constant over life
- Input Voltage: 120-277V or 347V, 50/60Hz
- Operating Temperature Range: 0°C + 35°C (32°F + 95°F)
- Total Harmonic Distortion: < 20%

CONTROLS

- Step dimming to 50%*
- Continuous dimming to 5% with 0-10V DC control protocol*
- Lutron EcoSystem[®] Enabled option allows seamless integration with Lutron EcoSystem controls
- Reference www.creelink.com/exLink.asp?70982140Z58R34126620963 for recommended dimming controls and wiring diagrams

REGULATORY & VOLUNTARY QUALIFICATIONS

- cULus Listed
- Suitable for damp locations
- Designed for indoor use
- UL924 (EB14 option)
- DLC qualified. Please refer to www.designlights.org/QPL for most current information
- RoHS compliant. Consult factory for additional details
- Meets FCC Part 15 standards for conducted and radiated emissions

Ambient Initial Lumens	Initial LMF	25K hr Projected ²	50K hr	75K hr	1001/1
Lamens		LMF	Projected ² LMF	Calculated ³ LMF	100K hr Calculated ³ LMF
0°C 22L, 31L, 4 and 50L	^{DL,} 1.05	1.04	1.04	1.04	1.04
(41°F) 40LHE	1.05	1.01	0.98	0.96	0.94
22L, 31L, 4 5°C and 50L	^{DL,} 1.04	1.03	1.03	1.03	1.03
(41°F) 40LHE	1.04	1.00	0.97	0.95	0.93
22L, 31L, 4 10°C and 50L	^{DL,} 1.03	1.02	1.02	1.02	1.02
(50°F) 40LHE	1.03	0.99	0.96	0.94	0.92
22L, 31L, 4 15°C and 50L	^{DL,} 1.02	1.01	1.01	1.01	1.01
(59°F) 40LHE	1.02	0.98	0.95	0.93	0.91
22L, 31L, 4 20°C and 50L	^{DL,} 1.01	1.00	1.00	1.00	1.00
(68°F) 40LHE	1.01	0.97	0.95	0.92	0.90
22L, 31L, 4 25°C and 50L	^{DL,} 1.00	0.99	0.99	0.99	0.99
(77°F) 40LHE	1.00	0.96	0.94	0.91	0.89
22L, 31L, 4 30°C and 50L	0L, 0.99	0.98	0.98	0.98	0.98
(86°F) 40LHE	0.99	0.95	0.93	0.91	0.89
22L, 31L, 4 35°C and 50L	0L, 0.98	0.97	0.97	0.97	0.97
(95°F) 40LHE	0.98	0.94	0.92	0.90	0.88
40°C 22L, 31L, 4 and 50L	DL, 0.97	0.96	0.96	0.96	0.96
(104°F) 40LHE	0.97	0.93	0.91	0.89	0.87

¹Lumen maintenance values at 25°C (77°F) are calculated per TM-21 based on LM-80 data and in-situ luminaire testing ²In accordance with IESNA TM-21-11, Projected Values represent interpolated value based on time durations that are within six times (6X) the IESNA LM-80-08 total test duration (in hours) for the device under testing ([DUT] i.e. the packaged LED chip) ³In accordance with IESNA TM-21-11, Calculated Values represent time durations that exceed six times (6X) the IESNA

In accordance with IESNA TM-21-11, Calculated Values represent time durations that exceed six times (6X) the IESNA LM-80-08 total test duration (in hours) for the device under testing ([DUT] i.e. the packaged LED chip)




T (800) 473-1234 F (800) 890-7507

Photometry

CR24-40L-30K BASED ON LTL REPORT TEST #: 24421

Luminaire photometry has been conducted by a NVLAP accredited testing laboratory in accordance with IESNA LM-79-08. IESNA LM-79-08 specifies the entire luminaire as the source resulting in a luminaire efficiency of 100%.



Coefficients Of Utilization – Zonal Cavity Method					
RC %:	80				
RW %:	70	50	30	10	
RCR: 0	119	119	119	119	
1	109	105	101	97	
2	100	92	85	79	
3	91	80	72	66	
4	83	71	63	56	
5	76	64	55	48	
6	71	57	48	42	
7	65	52	43	37	
8	61	47	39	33	
9	57	43	35	30	
10	53	40	32	27	
Effective Floor Cavity Reflectance: 20%					

Average Luminance Table (cd/m ²)								
	Horizontal Angle							
		0°	45°	90°				
ngle	45°	1,976	2,116	2,152				
Vertical Angle	55°	1,807	2,018	2,074				
Verti	65°	1,553	1,889	1,879				
	75°	1,149	2,348	1,119				
	85°	424	62	62				

Zonal Lumen Summary					
Zone	Lumens	% Lamp	Luminaire		
0-30	1,115	27.9%	27.9%		
0-40	1,835	45.9%	45.9%		
0-60	3,245	81.1%	81.1%		
0-90	4,000	100%	100%		
0-180	4,000	100%	100%		

Effective Floor Cavity Reflectance: 20%

Reference http://lighting.cree.com/products/indoor/troffers/cr-series for detailed photometric data

Application Reference Based on CR22-40L-30K Luminaire

Open Space						
Spacing	Initial Delivered Lumens	Lumens	Wattage	LPW	w/ft²	Average fc
	22L	2200	22	100	0.35	30
8 x 8	40L	4000	40	100	0.69	54
8 X 8	40LHE	4000	30.5	125	0.56	54
	50L	5000	50	100	0.78	68
	22L	2200	22	100	0.28	25
8 x 10	40L	4000	40	100	0.55	45
8 X 10	40LHE	4000	30.5	125	0.45	45
	50L	5000	50	100	0.62	57
	22L	2200	22	100	0.22	21
10 x 10	40L	4000	40	100	0.44	38
10 X 10	40LHE	4000	30.5	125	0.36	38
	50L	5000	50	100	0.50	48
	22L	2200	22	100	0.19	17
10 x 12	40L	4000	40	100	0.37	30
10 X 12	40LHE	4000	30.5	125	0.30	30
	50L	5000	50	100	0.42	38

9' ceiling: 80/50/20 reflectances; 2.5' workplane, open room. LLF: 1.0 Initial Open Space: 50' x 40' x 10'

© 2016 Cree, Inc. and/or one of its subsidiaries. All rights reserved. For informational purposes only. Content is subject to change. Patent www.cree.com/patents. Cree®, TrueWhite®, SmartCast®, and Cree TrueWhite® are registered trademarks, and the Cree logo, the Cree TrueWhite Technology logo, and CR24TM are trademarks of Cree, Inc. The UL logo is a registered trademark of UL LLC. Lutron®, Lutron EcoSystem®, EcoSystem®, and the Lutron EcoSystem Enabled logo are registered trademarks of Lutron, Inc. The DLC QPL logo is a registered trademark of Northeast Energy Efficiency Partnerships, Inc.



Canada: www.cree.com/canada