



# PL-C Cluster 2-Pin Base

## PL-C 26W/841/2P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information		Operating and Electrical	
Cap-Base	G24D-3 [ G24d-3]	LLMF 6000 h Rated	83 %
Life To 10% Failures (Nom)	6500 h	LLMF 8000 h Rated	81 %
Life To 50% Failures (Nom)	10000 h	Temperature	
LSF 2000 h Rated	99 %	Design Temperature (Nom)	28 °C
LSF 4000 h Rated	98 %	Controls and Dimming	
LSF 6000 h Rated	92 %	Dimmable	No
LSF 8000 h Rated	78 %	Mechanical and Housing	
Light Technical		Cap-Base Information	2 Pins
Color Code	840 [ CCT of 4000K (841)]	Approval and Application	
Luminous Flux (Nom)	1800 lm	Energy Efficiency Label (EEL)	B
Luminous Flux (Rated) (Nom)	1800 lm	Mercury (Hg) Content (Nom)	1.4 mg
Color Designation	Cool White (CW)	Energy Consumption kWh/1000 h	32 kWh
Chromaticity Coordinate X (Nom)	380		
Chromaticity Coordinate Y (Nom)	380		
Correlated Color Temperature (Nom)	4100 K		
Luminous Efficacy (rated) (Nom)	68 lm/W		
Color Rendering Index (Nom)	82		
LLMF 2000 h Rated	92 %		
LLMF 4000 h Rated	87 %		


## PL-C Cluster 2-Pin Base

### Product Data

Order product name	PL-C 26W/841/2P/ALTO 10PK
EAN/UPC - Product	046677111670
Order code	927906184030
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	927906184030
Net Weight (Piece)	64.300 g
ILCOS Code	F5Q-26/40/1B-I-G24d=3

### Dimensional drawing



Product	D	D1	A	B	C
PL-C 26W/841/2P/ALTO 10PK	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

PL-C 26W/840/2P

