



## Weatherproof Outlet Covers: Plastic & Extra-Duty Plastic

### WP5110C | Plastic In-Use Weatherproof Cover - Single-Gang



WP5110C

#### **PLASTIC IN-USE WEATHERPROOF COVER - SINGLE-GANG**

Plastic In-Use Weatherproof Covers are extra-duty rated and easy to install. Covers come with a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.



#### Features & Applications

##### Features

- Complies with 2014 NEC Article 406.9 (B)(1) for wet locations and extra-duty applications

##### Applications

- Industrial
- Commercial

- Exceeds CEC Article 26-702
- UL Certified for Type 3R outdoor enclosures
- NEW Faster Installation - Pre-Set for GFCI
- Meets requirements for cold impact testing: -60° F (-51° C)
- Heavy-duty UV stabilized polycarbonate cover, mounting base, and inserts
- 1/8" (3 mm) thick, pre-adhered neoprene gasket with slits for mounting screws
- Lockable hasp: All models accept up to 1/4" (6 mm) dia shank
- Impact rated: 12 lb. impact test to ensure cover remains intact
- Reinforced hinge pin designed to exceed 40 lb. hinge hang/stress test
- Warranty: 1-year limited
- Two inserts provided with all models for duplex and toggle/round
- No insert required for GFCI (up to 16 configurations)
- Max cord size: (2) #14 AWG or (1) #12 AWG
- Manufacturing
- Residential
- Agricultural
- Signage
- Athletic Fields

Specifications

Gang Type	Number of Included Inserts	Product Width (mm)
Single	3	119.1
Color	Weatherproof Cover Material	Product Depth (in)
Clear, Gray	UV Stabilized Plastic	3 5/8
Is Extra Duty Rated	Product Height (in)	Product Depth (mm)
Yes	6 1/3	92
Hinge Direction		Warranty

Horizontal, Vertical

Product Height (mm)

1-year limited

Insert Types Included

160.3

WP17

Product Width (in)

4 2/3

Videos

Related Accessories and Parts (2)



WP17

**SINGLE-GANG INSERTS**



WP10HP

**REPLACEMENT HINGE PINS (10-PC)**