

Specification Sheet

Part Number: 596-00206

WARNING: PHOTOVOLTAIC
POWER SOURCE

Solar Label, Reflective, Warning Photovoltaic Power Source, 6.5" x 1.0", V, Red, 50/roll

Article Number	596-00206
Type	PVPSR
Color	Red (RD)
Features & Benefits	<ul style="list-style-type: none">• Made with UV-stable inks and materials for durability and weather resistance.• Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.• Abrasion resistant for high-performance identification.• Meets NEC and IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.
Quantity Per	roll

Product Description	HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code (NEC) and the International Fire Code (IFC) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
Short Description	Solar Label, Reflective, Warning Photovoltaic Power Source, 6.5" x 1.0", V, Red, 50/roll
Global Part Name	PVPSR-505/281-RD
Technical Description	Pre-Printed Solar Label, Reflective, "WARNING: PHOTOVOLTAIC POWER SOURCE",6.5" X 1", Red
Local Order Number 2	Cross Reference = 10 per pack: 596-00676
Width W (Imperial)	6.5
Width W (Metric)	165.1
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Width of Liner (Metric)	28.57

Width of Liner (imperial)	1.125
Material	Type 505/281, UV-stabilized reflective vinyl with clear polyester laminate (505/281)
Material Shortcut	505/281
Adhesive	Acrylic
Halogen free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature (Metric)	-40°F to +174°F (-40°C to +79°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	NEC2011 IFC 2012 NEC2014 UL 969 NEC2017
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity(Imperial)	50
Package Quantity (Metric)	50

Customs Number	3919102055
-----------------------	------------

Labels per Column	1
--------------------------	---

Labels per Row	1
-----------------------	---

Weight (Metric)	0.521
------------------------	-------

Weight (Imperial)	1.14
--------------------------	------