



DuraMax Reflector Flood

65BR30/FL55/LL 120V 12/1

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Flood and Ambient Lighting
Gas Filling	Gas
Life With 3 Hour Per Day Use	2.3 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Light Technical	
Beam Angle (Nom)	55 °
Luminous Flux (Max)	620 lm
Luminous Flux (Nom)	610 lm
Beam Description	Flood
Correlated Color Temperature (Max)	2710 K
Correlated Color Temperature (Nom)	2690 K
Operating and Electrical	
Power (Rated) (Nom)	65 W

Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted
Cap-Base Information	Aluminium Cap
Filament Shape	CC6 [Straight]
Approval and Application	
Estimated Energy Cost Per Year	7.83 \$
Product Data	
Order product name	65BR30/FL55/LL 120V 12/1
EAN/UPC - Product	046677167684
Order code	920681636373
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	920681636373
Net Weight (Piece)	0.066 kg

DuraMax Reflector Flood

Dimensional drawing



65W E26 120V BR30 FL FR

Product
65BR30/FL55/LL 120V 12/1

