




Color :  White

UPC Code : 078477789674

Country Of Origin : Mexico

**Available Colors :**



## 5657-2W

15 Amp, 120/277 Volt, Decora Plus Rocker Double-Throw Ctr-OFF Momentary Contact Single-Pole AC Quiet Switch, Commercial Spec Grade, Self Grounding, Back & Side Wired, - White

Decora Plus devices combine designer styling with all the benefits of rugged Commercial Grade construction. The robust product offering includes: single pole, double pole, 3 and 4-way switches, momentary and maintained contact switches, as well as pilot light and illuminated switches.

### Technical Information

AC Horsepower Ratings

**HP Rating** : 1/2HP-120V 2HP-240V-277V

**Max. Amperage** : 12 Amp

Electrical Specifications

**Amperage** : 15 A

**Dielectric Voltage** : Withstands 1500V for 1 minute

**Endurance** : 30,000 cycles minimum

**Grounding** : Self-Grounding

**Overload UL20 Test** : 100 cycles of OL at 4.8 times rated current

**Temperature Rise** : Maximum 30 degrees C rise

**Voltage** : 120/277 VAC

Environmental Specifications

**Flammability** : Rated V-2 per UL 94

**Operating Temperature** : -40°C to 65°C

Material Specifications

**Actuator Material** : Thermoplastic

**Body Material** : Thermoplastic

**Color** : White

**Strap Material** : Steel

Mechanical Specifications

**Product ID** : Stamped on Strap

**Terminal Accom.** : 14-#10 AWG back wired; #14-#12 AWG side wired

**Terminal ID** : Brass-Hot Black-Hot White-Neutral Green-Gnd

**Termination** : Back or Side Wire

**Torque Range** : 12-14 inch pounds

Product Features

**Brand** : Decora Plus

**Color** : White

**Device Type** : Rocker Switch

**Feature** : Momentary Contact CTR OFF

**Function** : Single-Pole Double-Throw

**Grade** : Commercial Specification Grade

**Grounding** : Self-Grounding

**HP Rating** : 1/2HP-120V 2HP-240V-277V

**Voltage** : 120/277 VAC

Standards and Certifications

**ANSI** : C-73

**CSA C22.2 No. 111** : File #152105

**NEMA** : WD-1 & WD-6

**NOM** : 057

**UL Standard** : UL 20


**Warranty** : 10-Year Limited

### Dimensional Diagram



### Wiring Diagram

Single-Pole, Double Throw  
(SPDT) Center OFF



### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

