


KAYA™

FP7963RS 52" Wet Location Fan



	A	B
Fan w/4.5" downrod	18.48"	13.17"
Fan w/12" downrod	25.98"	20.67"
Fan w/18" downrod	31.98"	26.67"
Fan w/24" downrod	37.98"	32.67"
Fan w/36" downrod	49.98"	44.67"
Fan w/48" downrod	61.98"	56.67"
Fan w/60" downrod	73.98"	68.67"
Fan w/72" downrod	85.98"	80.67"

INSTALLATION REQUIREMENTS:

Ceiling fan attaches to electrical junction box securely anchored and capable of withstanding a load of at least 35 lbs.

ELECTRICAL REQUIREMENTS:

Ceiling fan requires a grounded electrical supply line of 120 volts AC, 60 Hz, 15 amp circuit.

MOTOR SPECS:

172 x 17 AC motor is designed for optimal performance with this fan.

BLADE SETS:

A set of five 21" reversible composite blades is included.

CONTROL OPTIONS:

Optional CW1, CW1SW, CW2, CW5, CWRL4 and CW60WH wall controls are available—sold separately. Optional BTR9, C4, CRL4WH and CRL8TS remote controls with receiver unit and BTR9 receiver unit are available—sold separately. Instructions are provided with each control.

LIGHTING OPTIONS:

One 26-watt GU24 CFL bulb included.

DOWNROD OPTIONS:

Fan comes with 1" dia. x 4.5" long downrod (DR1-45). Optional wet-location downrods (DR1SS) available in 12", 18", 24", 36", 48", 60", and 72" lengths. A downrod coupler is available for installations requiring a downrod longer than 72". Fan can be mounted on a sloped ceiling up to 27°. Most sloped ceiling installations require a downrod longer than the standard 4.5" downrod. Optional sloped ceiling ball kits (SCB1-52) are available for slope angles greater than 27° and up to 42°. Optional close-to-ceiling kit is available as well—sold separately. Call technical support for more information.

LOCATION USE:

Fan is rated for dry, damp and wet locations.

Available Finish

RS	Rust With Cherry Bronze Blade and Opal Frosted Glass
----	--

Airflow / Energy Efficiency Info (120V)

Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	155	4995	77	0.56	65
Med	106	3193	107	0.38	30
Low	60	1844	172	0.23	11

Energy Guide FTC

Power (W _{ave})	Total Air Delivery (CFM _{ave})	Estimated Yearly Energy Cost (\$)	Ceiling Fan Efficiency (CFM/W)
40	3617	11	90

Light Bulb Information (120V)

Bulb Type	Watts	QTY	Lumens Amount	Color Temp	CRI
GU24 / CFL	26	1	1600	2700	80%