



Material:

- The steel meets or exceeds the physical properties of ASTM A1011 GR 33, except with SS, ST & AL finishes.

Finishes:

- **Electrogalvanized (EG):** Conforms to ASTM B633, Type III SC1
- **Power-Strut Defender (DF):** Conforms to ASTM A1059
- **Hot Dip Galvanized (HG):** Conforms to ASTM A123 or A153
- **Perma-Gold (ZD):** Conforms to ASTM B633, Type II SC1
- **Stainless Steel, Type 304 (SS):** ASTM A240, Type 304 *
- **Stainless Steel, Type 316 (ST):** ASTM A240, Type 316 *
- **Aluminum (AL):** TBD

* These materials have different physical properties and performance characteristics. Please [contact us](#) for design support.

Material & Finish Combinations:

Material / Finish	Part Number Suffix	Pipe Clamp Material / Finish	Fasteners (Screw & Nut) Material / Finish	Example
Electro-galvanized	EG	EG	EG	PS 1100 1/2 EG
Hot-dipped galvanized	HG	HG	SS	PS 1100 1/2 HG
Power-Strut Defender	DF	DF	DF	PS 1100 1/2 DF
Stainless Steel Type 304	SS	SS	SS	PS 1100 1/2 SS
Stainless Steel Type 316	ST	ST	SS	PS 1100 1/2 ST
Aluminum	AL	AL	AL	PS 1100 1/2 AL

Part No.	Conduit Size	O.D. Size	Ga. (Thickness)	Finish	Product Weight / Piece (lbs)
PS 1100 2"	2"	2.375"	12 (2.7)	DF	0.36
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	DF	0.159
PS 1100 1"	1"	1.315"	14 (1.9)	EG	0.17
PS 1100 1"	1"	1.315"	14 (1.9)	EG	0.17
PS 1100 1"	1"	1.315"	14 (1.9)	DF	0.18
PS 1100 1"	1"	1.315"	14 (1.9)	HG	0.18
PS 1100 1"	1"	1.315"	14 (1.9)	HG	0.17
PS 1100 1"	1"	1.315"	14 (1.9)	SS	0.17
PS 1100 1"	1"	1.315"	14 (1.9)	ST	0.17
PS 1100 1"	1"	1.315"	14 (1.9)	AL	0.057
PS 1100 1"	1"	1.315"	14 (1.9)	AL	0.06
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	EG	0.11
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	EG	0.11
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	HG	0.117
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	SS	0.11
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	ST	0.11
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	AL	0.04
PS 1100 1/2"	1/2"	0.840"	16 (1.5)	AL	0.037
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	EG	0.29
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	EG	0.29
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	DF	0.307
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	HG	0.307
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	HG	0.29
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	ZD	0.29
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	SS	0.29
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	ST	0.29
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	AL	0.097
PS 1100 1-1/2"	1-1/2"	1.900"	12 (2.7)	AL	0.1
PS 1100 1-1/4"	1-1/4"	1.660"	14 (1.9)	EG	0.19
PS 1100 1-1/4"	1-1/4"	1.660"	14 (1.9)	EG	0.19
PS 1100 1-1/4"	1-1/4"	1.660"	14 (1.9)	DF	0.201
PS 1100 1-1/4"	1-1/4"	1.660"	14 (1.9)	HG	0.201
PS 1100 1-1/4"	1-1/4"	1.660"	14 (1.9)	SS	0.19
PS 1100 1-1/4"	1-1/4"	1.660"	14 (1.9)	ST	0.19

PS 1100 1-1/4 "	1-1/4"	1.660"	14 (1.9)	AL	0.063
PS 1100 1-1/4 "	1-1/4"	1.660"	14 (1.9)	AL	0.07
PS 1100 2"	2"	2.375"	12 (2.7)	EG	0.34
PS 1100 2"	2"	2.375"	12 (2.7)	EG	0.34
PS 1100 2"	2"	2.375"	12 (2.7)	HG	0.36
PS 1100 2"	2"	2.375"	12 (2.7)	HG	0.34
PS 1100 2"	2"	2.375"	12 (2.7)	SS	0.34
PS 1100 2"	2"	2.375"	12 (2.7)	ST	0.34
PS 1100 2"	2"	2.375"	12 (2.7)	AL	0.113
PS 1100 2"	2"	2.375"	12 (2.7)	AL	0.12
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	EG	0.4
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	EG	0.41
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	DF	0.424
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	HG	0.424
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	SS	0.4
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	ST	0.4
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	AL	0.14
PS 1100 2-1/2 "	2-1/2"	2.875"	12 (2.7)	AL	0.133
PS 1100 3"	3"	3.500"	12 (2.7)	EG	0.47
PS 1100 3"	3"	3.500"	12 (2.7)	EG	0.47
PS 1100 3"	3"	3.500"	12 (2.7)	DF	0.498
PS 1100 3"	3"	3.500"	12 (2.7)	HG	0.498
PS 1100 3"	3"	3.500"	12 (2.7)	SS	0.47
PS 1100 3"	3"	3.500"	12 (2.7)	ST	0.47
PS 1100 3"	3"	3.500"	12 (2.7)	AL	0.16
PS 1100 3"	3"	3.500"	12 (2.7)	AL	0.157
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	EG	0.15
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	EG	0.15
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	HG	0.159
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	SS	0.15
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	ST	0.15
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	AL	0.05
PS 1100 3/4"	3/4"	1.050"	14 (1.9)	AL	0.05
PS 1100 3/8"	3/8"	0.675"	16 (1.5)	EG	0.1
PS 1100 3/8"	3/8"	0.675"	16 (1.5)	EG	0.1
PS 1100 3/8"	3/8"	0.675"	16 (1.5)	HG	0.106
PS 1100 3/8"	3/8"	0.675"	16 (1.5)	SS	0.1
PS 1100 3/8"	3/8"	0.675"	16 (1.5)	ST	0.1
PS 1100 3/8"	3/8"	0.675"	16 (1.5)	AL	0.03
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	EG	0.62
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	EG	0.62
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	HG	0.657
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	SS	0.62
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	ST	0.62
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	AL	0.207
PS 1100 3-1/2 "	3-1/2"	4.000"	11 (3.0)	AL	0.21
PS 1100 4"	4"	4.500"	11 (3.0)	EG	0.67
PS 1100 4"	4"	4.500"	11 (3.0)	EG	0.67
PS 1100 4"	4"	4.500"	11 (3.0)	HG	0.71
PS 1100 4"	4"	4.500"	11 (3.0)	SS	0.67

PS 1100 4"	4"	4.500"	11 (3.0)	ST	0.67
PS 1100 4"	4"	4.500"	11 (3.0)	AL	0.223
PS 1100 4"	4"	4.500"	11 (3.0)	AL	0.223
PS 1100 5"	5"	5.563"	11 (3.0)	EG	0.8
PS 1100 5"	5"	5.563"	11 (3.0)	EG	0.8
PS 1100 5"	5"	5.563"	11 (3.0)	HG	0.848
PS 1100 5"	5"	5.563"	11 (3.0)	SS	0.8
PS 1100 5"	5"	5.563"	11 (3.0)	AL	0.267
PS 1100 6"	6"	6.625"	10 (3.4)	EG	1.02
PS 1100 6"	6"	6.625"	10 (3.4)	EG	1.02
PS 1100 6"	6"	6.625"	10 (3.4)	HG	1.081
PS 1100 6"	6"	6.625"	10 (3.4)	SS	1.02
PS 1100 6"	6"	6.625"	10 (3.4)	AL	0.35
PS 1100 8"	8"	8.625"	10 (3.4)	EG	1.3
PS 1100 8"	8"	8.625"	10 (3.4)	EG	1.3
PS 1100 8"	8"	8.625"	10 (3.4)	HG	1.378
PS 1100 8"	8"	8.625"	10 (3.4)	SS	1.3
PS 1100 8"	8"	8.625"	10 (3.4)	AL	0.4

Project:	<input type="text"/>		
Architect / Engineer:	<input type="text"/>		
Date:	<input type="text"/>	Phone:	<input type="text"/>
Contractor:	<input type="text"/>		
Address:	<input type="text"/>		
Notes:	<input type="text"/>		

Approval Stamp: