



1' x 4' LED panel lights provide smooth and uniform light edge-to-edge for a clean, modern look. For use in drop ceilings or drywall using the optional recessed mounting kit.

Color: White

Weight: 19.5 lbs

Project:

Type:

Prepared By:

Date:

Driver Info

Type: Constant Current
120V: 0.28A
208V: 0.17A
240V: 0.15A
277V: 0.13A
Input Watts: 33W
Efficiency: N/A

LED Info

Watts: 34W
Color Temp: 4000K
Color Accuracy: 83 CRI
L70 Lifespan: 100000
Lumens: 4334
Efficacy: 130 LPW

Technical Specifications

Listings

UL Listing:

Suitable for damp locations. Recommended for indoor use only.

DLC Listed:

This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities.
DLC Product Code: P00001726

IESNA LM-79 & LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

Construction

IC Rating:

Suitable for insulated ceilings

Lens:

High-transmission acrylic lens with excellent distribution and uniformity

Housing:

Lightweight housing is constructed of extruded aluminum

Installation:

Modular splice box/driver compartment for quick installation. Integral Tee-grid ceiling clips make installation easy and secure.

Finish:

Formulated for high-durability and long lasting color

Green Technology:

Mercury and UV-free. RoHS compliant components. Polyester powder coat finish formulated without the use of VOCs or toxic heavy metals.

LED Characteristics

LEDs:

Long-life, High efficiency, micro-power, surface mount LEDs; binned and mixed for uniform light output and color

Lifespan:

100,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

Color Consistency:

3-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

Electrical

Driver:

Constant Current, Class 2, 100-277V, 50/60Hz, 4kV Surge Protection, 700mA, 100-277V: 0.4A, Power Factor 99.5%

THD:

5.8% at 120V, 11.0% at 277V

Power Factor:

99.7% at 120V, 93.6% at 277V

Other

Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish.


Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

PANEL1X4-34N



Dimensions



Features

- Up to 60% savings on energy costs
- High-reflectance (91%) powder coat applied post fabrication for a more durable finish
- Ultra-smooth diffusion lens creates uniform light, edge to edge, for evenly lit spaces
- 100,000-hour LED Lifespan
- 5-Year, No-Compromise Warranty

Ordering Matrix

Family	Size	Wattage	Color Temp	Dimming
PANEL	1X4 = 1' x 4'	34 = 34W 41 = 41W 52 = 52W	Y = 3000K (Warm) YN = 3500K (Warm Neutral) N = 4000K (Neutral)	Blank = No Dimming /D10 = Dimmable