

SUBMITTAL SHEET

STEEL INSULATED EMT CONNECTORS COMPRESSION TYPE & RAIN-TIGHT

DESCRIPTION:

Orbit Industries' rain-tight compression connectors are used in wet locations to bond EMT thinwall conduits to electrical junction boxes or enclosures. Orbit Industries' rain-tight EMT compression connectors have been designed to comply with the new rain-tight test requirements along with the 2008 NEC 358.42 and 314.15 requirements. The steel construction ensures mechanical protection and the conduit to the designated electrical junction box or enclosure. With Orbit Industries' labor saving design, electrician can quickly tighten these connectors on EMT conduits.



FEATURES:

- Steel
- Zinc Electro-Plated
- Concrete-Tight
- Suitable for applications above 600V
- With Insulated Throat (Yellow, Throat color may vary)

CERTIFICATION:

UL file E310660, Conforms to UL 514B.



CONFIGURATION DATA:

Part No.	UPC	Trade Size	Std.Pkg.	Master Ctn
OF7601-SW	8-35243-05071-6	1/2"	25	250
OF7602-SW	8-35243-05075-4	3/4"	25	250
OF7603-SW	8-35243-05079-2	1"	10	100
OF7604-SW	8-35243-05083-9	1-1/4"	10	100
OF7605-SW	8-35243-05087-7	1-1/2"	10	50
OF7606-SW	8-35243-05091-4	2"	5	50
OF7607-SW	8-35243-05095-2	2-1/2"	-	12
OF7608-SW	8-35243-05099-0	3"	-	12
OF7609-SW	8-35243-05103-4	3-1/2"	-	6
OF7610-SW	8-35243-05107-2	4"	-	6

