







Project:
Location:
Cat.No:
Type:
Lamps: Qty:
Notes:

Philips Lightolier LyteCaster LED Adjustable Downlight is a low cost solution for slope ceiling and wall washing applications that features 30° tilt. Available in shallow new construction frame and IC remodeler. The downlight is damp location listed and interchangeable light engine/trim is available in 2 lumen packages.

Complete product = Frame-in kit + Adjustable light engine / Trim Order each separately

Ordering guide: Frame-In kit

Example: L6RAE1VA

Series L6R	Lumens ¹	Frame type	Dimming	Input voltage	Version VA
L6R LyteCaster 6" Round	blank 1500 20 2000	AirSeal IC, New Construction, Screw AN AirSeal IC, New Construction, Nail	E ELV dimming Z10 0-10V	1 120V U Universal	VA Version A ²
	15 1500 20 2000	R AirSeal IC, Remodeler			

Ordering guide: Adjustable light engine / Trim

Example: L6RA15827WVA

Series	Lumens ¹	CRI	сст	Finish	Version
L6RA				W	VA
L6RA LyteCaster 6" Round adjustable	15 1500 20 2000	8 80	27 2700K 30 3000K 35 3500K 40 4000K	W White (with white flange)	VA Version A ²
		9 90	27 2700K	W White (with white flange)	

Note : Lumen output is calculated based on 80 CRI and 3500K CCT. Please consult adjustment factors table on page 5 for other lumen outputs.

- 1. When ordering a Frame-in kit and a Light engine, the lumen package code must match.
- 2. Version A (VA) frames and light engines are not compatible with previous versions.







General purpose downlight

New construction frame-in kit


Bottom view



Side view



Adjustable light engine/trim



Maximum tilt: 30



Features

- Housing: .026" galvanized steel. UL listed for direct contact with thermal insulation. Airseal® housing minimizes air leakage to less than 2 CFM at 1.57PSF (or 75PA), which complies with the International Energy Conservation Code, and Washington State Energy Code (Section 502.4). This reduces heat loss and condensation in ceiling. Access door for inspection of junction box.
- 2. Lower frame and top cover: .026" galvanized steel. Accommodates ceilings up to 1½" (38mm) thick. 3/8" (9.5mm) deep integral lip with four notches at 90° apart to simplify alignment. Locks into position along length of mounting bars with locking screws.
- 3. Junction Box: 2.5" X 5 3/8" X 2" (27 cu. in) .032" galvanized steel. UL listed 90 ° supply conductors. Rated for branch circuit wiring supplying connected luminaires (daisy chaining).

- 4. **Retaining clips**: Permit easy and fast installation of light engine/trim.
- 5. Mounting bars: .059' galvanized steel. Bars pivot for easy attachment and wire-in below ceiling line. Bars extend to accommodate 16" (406mm) to 24" (610mm) O.C. joist spacing. Bars can accommodate 12" (305mm) O.C. joist spacing after a slight field modification (see Instruction sheet). Features integral self tapping phillips/ square drive screws for secure attachment to wood or metal construction. Also available with integral nails. Attaches to T-bar ceilings without the need of accessories. Bars installed on shortest dimension of frame, but can be easily repositioned 90 degrees from original position
- Driver: ELV: 120V, 50/60Hz.
 RoHS compliant, Class 2 power supply. Complies with FCC rules per Title 47 Part 15 (Class B) for EMI/RFI (conducted & radiated). Class A sound rating.

 O-10V: 120/277V, 50/60Hz.
 RoHS compliant, Class 2 power supply. Complies with FCC rules per Title 47 Part 15 (Class A) for EMI/RFI (conducted & radiated). Class A sound rating.
- 7. Ceiling cutout: 6 3/8" (162mm).

Electrical

Lifetime: Expected lifetime 50,000 hours and backed by a 5-year warranty. (see Philips.com/warranties for details)

Recommended dimmers

See LED-DIM Specification Sheet.


Labels

cULus Listed Type I.C., frames are suitable for damp location. Trims are cULus suitable for damp location. Complies with Air Leakage. Energy Star certified.


General purpose downlight

Remodeler kit


Bottom view



Side view



Side view



Features

- 1. Housing: .032 Aluminum. UL listed for direct contact with thermal insulation. Integral retaining spring secures housing to ceilings up to 2" thick. Removable for access to junction box and ceiling plenum. 5 1/2" maximum for use in 2" x 6" joist construction and shallow plenum applications. Airseal® housing minimizes air leakage to less than 2 CFM at 1.57PSF (or 75PA), which complies with the International Energy Conservation Code, and Washington State Energy Code (Section 502.4). This reduces heat loss and condensation in ceiling
- 2. **Junction Box:** 2 ½" x 2 ½" x 4 ¾" (29 cu in.) .031" galvanized steel. UL listed for 90°C supply conductors. Rated for branch circuit wiring supplying connected fixtures.

- 3. **Retaining clips:** Permit easy and fast installation of light engine/trim.
- 4. **Driver: ELV /Triac:** 120V, 50/60Hz. RoHS compliant, Class 2 power supply. Complies with FCC rules per Title 47 Part 15 (Class B) for EMI/RFI (conducted & radiated). Class A sound rating.
 - **0-10V**: 120/277V, 50/60Hz. RoHS compliant, Class 2 power supply. Complies with FCC rules per Title 47 Part 15 (Class A) for EMI/RFI (conducted & radiated). Class A sound rating.
- 5. Ceiling cutout: 6 3/4" (162mm).

Electrical

Lifetime: Expected lifetime 50,000 hours and backed by a 5-year warranty. (see Philips.com/warranties for datally)

Recommended dimmers


See LED-DIM Specification Sheet.

Labels

cULus Listed Type I.C., frames are suitable for damp location. Trims are cULus suitable for wet location (no shower lens unit required). Complies with Air Leakage. Energy Star certified.

General purpose downlight

Reflector: Round adjustable



Electrical specifications

Frame-in kit / Remodeler		Input	Input	Input	LED drive	Input	LED	THD	Power
	Lumens	volts	freq.	current	current	power	power	factor	factor
L6RAE1VA / L6R15RE1VA	1500	120V	50/60Hz	0.14A	350mA	16W	13W	<20%	>0.9
L C D A 710 L I V A / L C D 15 D 710 L I V A	1500	120V	50/60Hz	0.14A	350mA	17W	13W	<10%	>0.9
L6RAZ10UVA / L6R15RZ10UVA		277V	50/60Hz	0.07A	350mA	17W	15W	<15%	>0.9
L6R20AE1VA / L6R20RE1VA	2000	120V	50/60Hz	0.175A	470mA	19W	16W	<20%	>0.9
L6R20AZ10UVA / L6R20R10UVA	2000	120V	50/60Hz	0.26A	470mA	20W	16W	<10%	>0.95
LORZUAZ IUUVA / LORZUR IUUVA	2000	277V	50/60Hz	0.11A	470mA	20W	16W	<15%	>0.95

General purpose downlight

80 CRI, 1500 lumens (downlight photometry shown)

Candela Curves
200
400
600
-800

Angle	Mean CP	Lumens
0	730	
5	724	69
10	412	
15	698	197
20	671	
25	634	292
30	596	226
35 40	538 473	336
45	397	304
50	314	304
55	235	210
60	161	
65	107	111
70	80	
75	59	62
80	37	
85	16	18
90	0	

Frame: L6RAE1VA/L6RAZ10UVA/L6R15RE1VA/L6R15RZ10UVA Light engine: L6R15835VA Trim: L6RDW Report no3: 686GFR

Output lumens: Input Watts1: 16 W Spacing Criterion: 1.2

Efficacy: 99.9lm/W CCT2: 3500 K CRI: ≥80

Single unit data

Height to	Initial Center Beam	Beam
Lighted Plane	Foot-Candles	Dia. (ft)*
5'	29	6.0'
6'	20	7.2'
7'	15	8.4'
8'	11	9.6'
9'	9	10.8'

^{*} Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing Initial Center Beam on center Foot-Candles	Watts per Sq. Ft.
5' 66.8	0.71
6' 43.8	0.47
7' 31.3	0.33
8' 26.1	0.28
9' 20.9	0.22

38'x38'x10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Coefficients of utilization


Cei	iling	80%			70)%	50)%	30)%	0%	
Wa	ıll	70	50	30	10	50	10	50	10	50	10	0
RC	R	Zona	Zonal cavity method - Effective floor reflectance = 2					20%				
	0	119	119	119	119	116	116	111	111	106	106	100
_	1	110	106	102	99	104	97	100	94	96	92	87
ξį	2	102	94	88	83	92	82	89	80	86	79	75
Ratio	3	94	84	77	71	83	71	80	69	77	68	65
≥	4	86	76	68	62	74	61	72	60	70	60	57
Cavity	5	80	68	60	54	67	54	65	53	63	53	50
ΰ	6	74	62	54	48	61	48	59	47	58	47	45
Ē	7	69	57	48	43	56	43	54	42	53	42	40
Room	8	65	52	44	38	51	38	50	38	49	38	36
œ	9	60	48	40	35	47	35	46	35	45	34	33
	10	57	44	37	32	44	32	43	32	42	31	30

Zonal lumens & percentages				
Zone	Lumens	%Luminaire		
0-30	5558	3476%		

Zone	Lumens	%Luminaire	90CRI 2700K: = 0.71
0-30	5558	347.6%	80CRI 2700K: = 0.89
0-40	893	55.9%	80CRI 3000K: = 0.97
0-60 0-90	1408 1599	88.1% 100.0%	80CRI 3500K: = 1.00

CRI and CCT adjustment factors

80 CRI, 2000 lumens (downlight photometry shown)



Angle	Mean CP	Lumens
0	863	
5	856	81
10	843	
15	818	230
20 25	778 730	336
25 30	671	330
35	604	377
40	529	3//
45	448	345
50	365	
55	284	254
60	205	
65	137	141
70	98	
75 80	70 43	74
85	43 19	22
90	0	
50		

Frame: L6R20AZ20UVA/L6R20AE1VA/ L6R20RZ10UVA/L6R20RE1VA Light engine: L6R20835VA Trim: L6RDW

Report no³: 891GFR

Output lumens: 1859 lm Input Watts1: 19.8 W Spacing Criterion: 1.1

Efficacy: 93.9lm/W CCT^2 3500 K

Single unit data

Height to Lighted Plane	Initial Center Beam Foot-Candles	Beam Dia. (ft)*	
5'	35	5.5'	
6'	24	6.6'	
7'	18	7.7'	
8'	13	8.8'	
9'	11	9.9'	

^{*} Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial Center Beam Foot-Candles	Watts per Sq. Ft
5' 6' 7' 8'	77.5 50.8 36.3 30.3 24.2	0.88 0.58 0.41 0.34 0.27
9	24.2	0.27

38'x38'x10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Coefficients of utilization

Ceiling		80%			70%		50%		30%		0%	
Wal	l	70	50	30	10	50	10	50	10	50	10	0
RCF	?	Zona	al cav	ity m	etho	d - Ef	fectiv	e flo	or ref	lecta	nce =	20%
	0	119	119	119	119	116	116	111	111	106	106	100
_	1	110	106	102	99	104	97	100	94	96	91	87
Ratio	2	101	94	88	83	92	82	89	80	86	78	75
æ	3	93	84	77	71	82	70	79	69	77	68	65
≥	4	86	75	67	61	74	61	72	60	69	59	56
Cavity	5	80	68	60	54	67	53	65	53	63	52	50
	6	74	62	53	47	61	47	59	47	57	46	44
Ε	7	69	56	48	42	55	42	54	42	53	42	39
Room	8	64	52	44	38	51	38	50	38	48	38	36
œ	9	60	48	40	35	47	35	46	34	45	34	32
	10	57	44	37	32	44	32	43	31	42	31	29

Zonal lumens & percentages

Zone	Lumens	%Luminaire
0-30	647	34.8%
0-40	1023	55.1%
0-60	1622	87.3%
0-90	1859	100.0%

CRI and CCT adjustment factors				
90CRI 2700K: = 0.71				
80CRI 2700K: = 0.89				
80CRI 3000K: = 0.97				

80CRI 3500K: = 1.00

- 1. Wattage: controlled to within ± 5%
- 2. Correlated Color Temperature: within specs as defined in ANSI_NEMA_ANSLG C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.
- 3. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. philips.com/luminaires



Philips Lighting North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008