

TYPE T3A

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro tin plated
- Chamfered wire entry
- UL Listed and CSA Certified for 2000 volts, 90° C
- Must be mounted with a minimum of 2 bolts

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- Ensures reliability for copper or aluminum conductors

C




Fig. 1



Fig. 2



Fig. 3

Catalog Number	Figure Number	Wire Range	Bolt Size	Dimensions									Hex Size
				C	E	F	G	H	J	K	R	T	
T3A2-2	1	Three: 2-14	5/16	11/32	1-11/16	2-3/16	11/32	1-19/32	7/8	3/16	5/8	13/16	Slot
T3A2-0	1	Three: 1/0-14	3/8	7/16	2-5/32	2-29/32	11/32	1-15/16	1	1/4	7/8	15/16	Slot
T3A2-3/0N	1	Three: 3/0-6	1/2	9/16	3	3-7/8	5/8	2-13/16	1-3/4	5/16	1-1/8	1-1/2	5/16
T3A2-250N	1	Three: 250kcmil-6	1/2	9/16	3	4	5/8	2-13/16	1-3/4	5/16	1-3/16	1-17/32	5/16
T3A2-350N	1	Three: 350kcmil-6	1/2	9/16	3	4-5/16	5/8	3	1-3/4	5/16	1-3/8	1-17/32	5/16
T3A2-600N*	3	Three: 600kcmil-2	1/2	9/16	3-1/4	5-1/2	5/8	3-1/2	1-3/4	3/8	1-1/2	1-49/64	3/8
T3A2-800N*	3	Three: 800kcmil-350kcmil	1/2	9/16	3-5/8	5-31/32	5/8	4-1/8	1-3/4	1/2	1-13/16	2-21/64	5/16
T3A2-1000N*	3	Three: 1000kcmil-500kcmil	1/2	9/16	3-5/8	5-31/32	5/8	4-7/8	1-3/4	1/2	1-13/16	2-21/64	3/8
T3A4-2	2	Three: 2-14	5/16	11/32	1-11/16	2-3/16	11/32	1-19/32	7/8	3/16	5/8	13/16	Slot
T3A4-0	2	Three: 1/0-14	3/8	7/16	2-5/32	2-29/32	11/32	1-15/16	1	1/4	7/8	15/16	Slot
T3A4-3/0N	2	Three: 3/0-6	1/2	9/16	3	3-7/8	5/8	2-13/16	1-3/4	5/16	1-1/8	1-1/2	5/16
T3A4-250N	2	Three: 250kcmil-6	1/2	9/16	3	4	5/8	2-13/16	1-3/4	5/16	1-3/16	1-17/32	5/16
T3A4-350N	2	Three: 350kcmil-6	1/2	9/16	3	4-5/16	5/8	3	1-3/4	5/16	1-3/8	1-17/32	5/16
T3A4-600N*	3	Three: 600kcmil-2	1/2	9/16	3-1/4	5-1/2	5/8	3-1/2	1-3/4	3/8	1-1/2	1-49/64	1/2
T3A4-800N*	3	Three: 800kcmil-350kcmil	1/2	9/16	3-5/8	5-31/32	5/8	4-1/8	1-3/4	1/2	1-13/16	2-21/64	1/2
T3A4-1000N*	3	Three: 1000kcmil-500kcmil	1/2	9/16	3-5/8	5-31/32	5/8	4-7/8	1-3/4	1/2	1-13/16	2-21/64	1/2

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)
DE-OX Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A/B, UL File E6207

* Mounting hole spacing from side to side, hole to hole is .875