



Part Number: 5500FE

Security & Sound, 2 Conductor 22 AWG, TC, Shielded, CMR

Product Description

Security & Sound Cable, Riser-CMR, 2-22 AWG stranded tinned copper conductors with polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

Environmental Space:	Indoor - Riser
Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	7x30	TC - Tinned Copper	2

Conductor Count:	2
Conductor Size:	22 AWG

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.045 in	0.008 in

Color Chart

Number	Color
1	Black
2	Red

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	Solid

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.126 in	0.017 in	Yes

Construction and Dimensions

Cabling

Lay Length	Lay Direction	Twists
2.5 in	Left Hand	4.8 twist/ft

Print Legend:	NEW GENERATION(R) BY BELDEN 5500FE CMR 75C 2C22 SHIELDED (UL) E108998 OR C(UL) CMG (2 FT., 7 DIGIT SEQUENTIAL) FEET
---------------	---

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
16.1 Ohm/1000ft	16.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
---	---

34.5 pF/ft	62 pF/ft
------------	----------

Shielding:	Foil(s) or Copper Tape(s)
------------	---------------------------

Current

Element	Max. Recommended Current [A]
10C Temperature Rise	2.8 Amps per conductor @ 25°C A

Current Table Note:	10C Temperature Rise
---------------------	----------------------

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	10.0 lbs/1000ft
Max Recommended Pulling Tension:	23.7 lbs
Min Bend Radius/Minor Axis:	1.5 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6500FH

Part Number

Variants

Item #	Color
5500FE 010U1000	Black

5500FE.00153	Chrome
5500FE.00152	Gray
5500FE.00305	Gray
5500FE.00U305	Gray
5500FE 0081000	Gray
5500FE 008500	Gray
5500FE 008U1000	Gray
5500FE 008U500	Gray
5500FE 009U1000	White

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.