

DESCRIPTION

High efficiency, low brightness 6-inch aperture medium beam reflector for use with compact fluorescent lamps. The precisely formed non-imaging optical reflector ensures 55° cutoff to lamp and lamp image and the one piece design eliminates light leaks at the ceiling. Adjustable socket locks lamp into optimal position and cannot be disturbed by normal maintenance. Standard features include low iridescent finish on all reflector colors and venting to ensure maximum lamp life and lumen output. Optics offer unparalleled performance in glare free lighting with a smooth beam devoid of hot spots. Medium beam, wide beam, lensed, and open wall wash reflectors are interchangeable within the same housing.

SPECIFICATION FEATURES

Optical Reflector

.050 thick aluminum, in a one piece spun parabolic contour. Available in a variety of Alzak® finishes. Also available with white or black baffle. Positive reflector mounting, without tools, pulls trim tight to ceiling.

Trim Ring Options

Self flanged or molded white ring. Rimless trim ring accessory available.

Socket Cap

One piece vented and finned die cast aluminum cap for maximum thermal performance..

Mechanical Housing  
Mounting Frame

One piece precision die cast aluminum 1-1/2" deep collar accommodates varying dimensions of ceiling materials.

Universal Mounting Bracket

Accepts 1/2" EMT, C Channel, T bar fasteners, and bar hangers. Adjusts 5" vertically from above or below ceiling.

Conduit Fittings

Die cast screw tight connectors.

Junction Box

Listed for eight #12AWG (four in, four out) 90°C conductors feed through branch wiring. 1/2" and two 3/4" pry outs. Positioned to allow straight conduit runs. Access to junction box by removing reflector.

Socket

4-pin GX24q3/4 fatigue free stainless steel lamp spring ensures positive lamp retention.  
26/32/42W GX24q3/4  
18W G24q2  
13W G24q1

Electronic Ballast with  
Quick Disconnect

Electronic ballast provides full light output and rated lamp life. Provides flicker free and noise free operation and starting. End of lamp life protection is standard.

Labels


cULus listed, standard damp label. Electronic ballast housings include peel down wattage label from 42W down to 26W allowing de-rating to meet max wattage requirements. Meets IECC, ASHRAE, and Title 24 commercial standards.




**CD6013  
CD6018  
CD6042  
6CV142M**

**13 or 18W DTT  
26/32/42W TTT or PLT  
Compact Fluorescent**

**6-Inch Vertical  
Medium Beam Downlight**



Top View




EXAMPLE: CD6042E 6CV142M1LI

Housing	Ballast	Options	Trims	Finish	Option	Accessories
<b>CD6013</b> =6" vertical 13W DTT lamp <b>CD6018</b> =6" vertical 18W DTT lamp <b>CD6042</b> =6" vertical 26/32/42TTT lamp	<b>E</b> =120/277V 50/60 Hz Electronic <b>3E</b> =347V 50/60 Hz Electronic electronic <b>EDR26</b> =26W Derated label electronic <b>EDR32</b> =32W Derated label electronic <b>D5LT</b> =18W 120-277V Fifth Light (DALI Dimming) (CD6018 only) <b>D5LT42</b> =42W 120-277V Fifth Light (DALI) Dimming <b>D5LT32</b> =32W 120-277V Fifth Light (DALI) Dimming <b>D5LT26</b> =26W 120-277V Fifth Light (DALI) Dimming <b>3D5LT32</b> =32W 347V Fifth Light (DALI) Dimming <b>3D5LT26</b> =26W 347V Fifth Light (DALI) Dimming <b>D26/32</b> =26W or 32W 120-277V Dimming, Lutron EcoSystem/ 3-Wire Control (Factory Wired for 3-Wire) <b>D</b> =120-277V Dimming Lutron EcoSystem/ 3-Wire Control (Factory Wired for 3-Wire) <b>D26MARKVII</b> =26W 120-277V Advance MARK7 <b>D32MARKVII</b> =32W 120-277V Advance MARK7 <b>D42MARKVII</b> =42W 120-277V Advance MARK7 <b>DMARKVII</b> =18W 120-277V Advance MARK 7 (CD6018 only) <b>1D26MARKX</b> =26W 120V Advance MARK 10 <b>1D32MARKX</b> =32W 120V Advance MARK 10 <b>1D42MARKX</b> =42W 120V Advance MARK 10 <b>2D26MARKX</b> =26W 277V Advance MARK 10 <b>2D32MARKX</b> =32W 277V Advance MARK 10 <b>2D42MARKX</b> =42W 277V Advance MARK 10 <b>1DMARKX</b> =18W 120V Advance MARK 10 (CD6018 only) <b>2DMARKX</b> =18W 277V Advance MARK 10 (CD6018 only)	<b>CP</b> =Chicago Plenum <b>EM</b> =Emergency Module with remote test switch <sup>2</sup> <b>IEM</b> =Emergency Module with Integral Test Switch <sup>2</sup>	<b>6CV142M1</b> =6" medium beam reflector self flanged <b>6CV142M0</b> =6" medium beam reflector with polymer trim ring <b>6CV142M1E</b> =6" medium beam reflector self flanged, for integral emergency <b>6CV142M0E</b> =6" medium beam reflector polymer trim ring, for integral emergency	<b>Alzak® Finishes</b> <b>LI</b> =Specular Clear <b>H</b> =Semi-Specular Clear <b>WMH</b> =Warm Haze <b>G</b> =Gold <b>WH</b> =Wheat <b>WHH</b> =Wheat Haze <b>GP</b> =Graphite <b>GPH</b> =Graphite Haze <b>B</b> =Black <b>Painted Finishes</b> <b>W</b> =Gloss White <b>WB</b> =White Baffle (polymer trim ring only) <b>BB</b> =Black Baffle (polymer trim ring only)	<b>WF</b> =White Painted Flange	<b>HB26</b> =C Channel Bar Hangers, 26" Long, Pair <b>HB50</b> =C Channel Bar Hangers, 50" Long, Pair <b>TRRC6</b> =Rimless Trim Ring, White <sup>1</sup> <b>FK5</b> =5 Amp Field Installable Fuse Kit 300V Max <b>RMB22</b> =Wood Joist Bar Hanger, 22" Long, Pair <b>HSAC6</b> =Slope Adapter for 6" Aperture Housings, Specify Slope <b>TRMC6</b> =CFL Metal Trim Ring <sup>1</sup>

Notes: <sup>1</sup> Order trim with polymer trim ring. <sup>2</sup> Not available with Chicago Plenum.  
 (Consult specification sheet for ordering information and options).

## PHOTOMETRICS

## Candlepower Distribution Curve



Test No. P13271  
 CD6042E 6CV142M1LI  
 Lumens = 2400  
 Efficiency = 67.1%  
 Lamp = 32W TTT  
 SC = 1.32-1.31

## Cone of Light

Distance Fixture to Lighted Plane	Initial Footcandles at Nadir	Beam Diameter
5.5'	31	6.6'
7.5'	17	9'
8'	15	9.6'
10'	10	12'
12'	7	14.6'

## Candela Distribution

Degrees Vertical	Candela
0	946
5	960
15	899
25	840
35	690
45	417
55	130
65	7
75	2
85	0
90	0


## Zonal Lumen Summary

Zone	Lumens	%Fixture
0-30	731	45.4
0-40	1159	72.0
0-60	1599	99.3
0-90	1610	100.0
90-180	0	0.0
0-180	1610	100.0

## Luminance

Average Candela/M <sup>2</sup>	Avg. 0° Luminance
45	28627
55	11002
65	804
75	375
85	0

## Candlepower Distribution Curve



Test No. P13387  
 CD6042E 6CV142M1LI  
 Lumens = 2400  
 Efficiency = 0.584%  
 Lamp = 32W PLT  
 SC = 1.31 - 1.31

## Cone of Light

Distance Fixture to Lighted Plane	Initial Footcandles at Nadir	Beam Diameter
5.5'	26	7'
7.5'	14	9.6'
8'	12.3	10.2'
10'	7.9	12.8'
12'	5.5	15.4'

## Candela Distribution

Degrees Vertical	Candela
0	776
5	796
15	810
25	769
35	623
45	362
55	65
65	3
75	1
85	0
90	0

## Zonal Lumen Summary

Zone	Lumens	%Fixture
0-30	658	46.9
0-40	1046	74.6
0-60	1394	99.4
0-90	1402	100.0
90-180	0	0.0
0-180	1402	100.0

## Luminance

Average Candela/M <sup>2</sup>	Avg. 0° Luminance
45	24851
55	5501
65	345
75	188
85	0