

QuickConnect Cable

Catalog#	Prepared by
Project	Date
Comments	Type

Overview


The QuickConnect cables, couplers and splitters connect the Room Controller and devices simplifying the Click & Go connection enabling automatic functionality upon power up. Cables are pre-terminated with industry standard RJ45 connectors.

Features

- Pre-terminated cables in lengths up to 100 feet
- Available in plenum and non-plenum rated
- Automatically included as part of the QuickKit

**EAT•N***Powering Business Worldwide*

Specifications

Electrical Rating	Class 2, LPS
Voltage	24 VDC supplied from Room Controller
Operating Environment	Temperature: 32°F to 104°F (0°C to 40°C) Relative Humidity: Less than 95%, non-condensing For indoor use only
Standards	UL 508 Listed 

Description/Operation

QuickConnect cables are plugged into ports on the Room Controller and Room Controller devices creating a local room based network that works out-of-the-box providing a superior energy savings control sequence with intuitively engraved wallstations.

Installation

Low voltage devices are connected to the Room Controllers using provided QuickConnect cables.

Ordering

Catalog #	Description
GGRC-COUPLER	RJ45 Coupler
GGRC-SPLITTER	RJ45 Splitter
GGRJ45-006-G	RJ45 cables 6 inches
GGRJ45-03-G	RJ45 cables 3 feet
GGRJ45-10-G	RJ45 cables 10 feet
GGRJ45-25-G	RJ45 cables 25 feet
GGRJ45-50-G	RJ45 cables 50 feet
GGRJ45-100-G	RJ45 cables 100 feet
GGRJ45-10P-G	RJ45 cables 10 feet plenum rated
GGRJ45-25P-G	RJ45 cables 25 feet plenum rated
GGRJ45-50P-G	RJ45 cables 50 feet plenum rated
GGRJ45-100P-G	RJ45 cables 100 feet plenum rated

*The Room Controller QuickKit automatically includes recommended cable quantities and lengths based on the installed room type and number of devices.

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Eaton's Cooper Controls Business
203 Cooper Circle
Peachtree City, GA 30269
coopercontrol.com

© 2014 Eaton
All Rights Reserved
Printed in USA
Publication No. ACC140970
November 3, 2014