



STAINLESS STEEL FDC SINGLE GANG DEVICE BOXES

Features:

- Manufactured in type 316 stainless steel for increased corrosion resistance
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Machined standard NPT threads Internal grounding screw included
- Manufactured with mounting feet
- Ports located on the top & bottom
- No package qty. required

Certifications and Compliances:

- UL/cUL 514A Listed
- File #E307133
- Intended for installation in accordance with Article 314 of ANSI/NFPA 70, National Electrical Code (NEC)

Material

- Body - 316SS
- Grounding Screws - 316SS
- Washer - Brass



Applications:

Used for wiring devices, such as switches and receptacles.

Industries Commonly Served:

- Food & Beverage Production
- Marine & Coastal Facilities
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Pulp & Paper Mills
- Along with other corrosive environments

Part Number	Size	Overall Length	Overall Width	Depth	Cubic in.	Center Hole to Center Hole	Mounting Feet Hole Dia.	Weight each per lb
S60700FDCS	3/4"	6.250"	2.850"	2.650"	25"	3.250"	5/16"	2.48
S61000FDCS	1"	6.300"	2.850"	2.650"	25"	3.250"	5/16"	3.10

*All dimensions are for informational purposes only *Tolerances +/- 5%*