

CANNON 10K™

Faster

- 4 Speed dual capstan
- 9' & 18' (per min.) on low speed
- 20' & 40' on high speed
- Self contained ready to pull
- Quickly change from side pull to overhead, underground or truck hitch
- No gang box of parts
- Adjustable counter-balance for easy setup and a 15 lb. working weight
- Pulls out almost 10' of extra wire
- Universal adapter sits on the conduit lock nut, fits a wide range of sizes, and often eliminates the need to use the conduit adapters on lighter pulls

Safer

- No anchoring required in most situations
- Easy to transport
- Ergonomic balance point
- Telescoping and collapsible
- User stands to the side during pulls
- Easily maneuvers into tight spaces
- Length (fully extended) 10'6"
- Width 30"

Smarter

- Open front conduit adapters allow for easy removal at the end of the pull from the top, eliminating the need for any disassembly to pull additional wire
- Super duty puller will perform on every wire pull
- Collapsible stores and transports easily
- Interchangeable components for adaptability on the job site
- Use rope designed for pulling with a minimum tensile strength of 26,000 lb.
- Easily extend boom with 2.5" rigid conduit

Includes

- Cannon 10K[™] cable puller (total weight 308 lb.)
- Universal adapter
 for loads under 5,000 lb.
- 5 Conduit adapters sizes 2" through 4" (5" & 6" also available)
- Powered by a 20 amp, 2 speed coring motor with built-in slip clutch
- Foot switch (UL standard)
 NOTE: Patented

NUIE: Patented

Model Description

C10K Cannon 10K - 10,000 lb. Wire Puller





150818_FL_iTOOLco1



TWO PULLERS IN ONE — Hi-Speed 5K / Hi-Torque 10K



Force Gauge Available



Low Torque - 5K Pulls



High Torque - 10K Pulls