



# PAR38 LED

## 17PAR38/S15 4000 DIM AF SO 6/1

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

### Product data

<b>General Information</b>			
Cap-Base	E26 [ Single Contact Medium Screw]	Lamp Current (Nom)	167 mA
Nominal Lifetime (Nom)	25000 h	Wattage Equivalent	100 W
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	17-100W	Warm Up Time To 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.85
		Voltage (Nom)	120 V
<b>Light Technical</b>			
Color Code	841 [ CCT of 4100K (841)]	<b>Temperature</b>	
Beam Angle (Nom)	15 °	T-Case Maximum (Nom)	
Initial lumen (Nom)	1300 lm	89 °C	
Luminous Flux (Rated) (Nom)	1300 lm		
Luminous Intensity (Nom)	11000 cd	<b>Controls and Dimming</b>	
Color Designation	Cool White (CW)	Dimmable	
Rated Beam Angle	15 °	Yes	
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	77 lm/W	<b>Approval and Application</b>	
Color Consistency	<6	Energy star mark	
Color Rendering Index (Nom)	80	Suitable For Accent Lighting	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Label (EEL)	
		Not applicable	
<b>Operating and Electrical</b>			
Input Frequency	60 Hz	<b>Product Data</b>	
Power (Rated) (Nom)	17 W	Order product name	
		120V PAR38 17W 15D 4000K 1200 D AF SO	
		EAN/UPC - Product	
		046677435370	
		Order code	
		435370	
		Numerator - Quantity Per Pack	
		1	


PAR38 LED

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001113304
Net Weight (Piece)	0.001 kg

Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- CAUTION: Risk of electric shock - do not use where directly exposed to water.
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005

Dimensional drawing



Par38 CL 120V 17W-120W 15D 4000K E26 D

Product	D	C
120V PAR38 17W 15D 4000K 1200 D AF SO	120.3 mm	130.5 mm

Photometric data

