



SPECIFICATIONS

GENERAL:

- HEIGHT: 8-3/4"
- WIDTH: 20-1/2"
- EXTENSION: 5-1/8"
- IN/OUT: INDOOR DAMP

MATERIALS:

- GLASS: OPAL GLASS
- REPLACEMENT GLASS: G2533

ELECTRICAL:

- F2533-80:
3 MEDIUM BASE 100 WATT MAX
A19 LAMPS NOT INCLUDED 120 VOLTS
- F2537-80:
3 GU24 BASE 13 WATT MAX
BULB INCLUDED



MOUNTING:

- WALL

FINISHES:

- BRIGHT SATIN NICKEL - 80 (BSN) 

Please contact your representative for more color options.