

EL2699RA

3" Low Voltage Remodel Housing with 12 Volt Thermally Protected Magnetic Transformer.



PROJECT INFORMATION:

Project Name: _____

Fixture Type: _____

Date: _____

DIMENSIONS



PRODUCT SPECIFICATIONS

Housing Features: For use in existing ceilings. Thermally protected magnetic transformer. Single wall construction.

The **EL2699RA** housing meets restricted air flow requirements (Per ASTM-E283 Standards).

Lamp: 12W Max 12V MR16 GU/GX5.3 bi-pin LED/Halogen (not included, by others)

Transformer: 120V/12V/50W Magnetic AC.

Lamp Holder: MR16 GU/GX5.3 bi-pin socket

Note: Use only dimmers specifically designed for used with magnetic transformer. Low voltage luminaries may produce audible sound when used with dimmers.

INSTALLATION

Junction Box : Pre-wired junction box provided with 1/2" and 3/4" knockout. U.L. listed/C.U.L. listed: for through branch wiring, maximum (8) No. 12 AWG branch circuit conductors (4 in, 4 out). Junction box provided with removable access plates.

Mounting: (4) remodel clips secure housing and accommodate various ceiling thicknesses.

Mounting Frame: Stamped galvanized steel material and painted for corrosion resistance.

Labels: • U.L. listed for damp locations
• U.L. listed for feed through

CATALOG NUMBER

Example: EL2699RA

See trims page for variety of trims available.

2042 East Vernon Avenue, Vernon, CA 90058 • Tel: (323) 231-2600 Fax: (323) 231-3200 • www.elcolighting.com

© ELCO LIGHTING 2013 All Rights Reserved. Rev. May 2015. ELCO Lighting reserves the right to make specification and design changes without notice. LIGHTING

ELCO
LIGHTING

