



Energy Saver GU24

EL/mdTQS 13W GU24

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Product data

General Information	
Cap-Base	GU24 [GU24]
Bulb Shape	EL/mdTQS
Nominal Lifetime (Nom)	10000 h
Switching Cycle	5000X
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	900 lm
Luminous Flux (Rated) (Nom)	900 lm
Color Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Nom)	70 %
Chromaticity Coordinate X (Nom)	459
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	50 %

Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	13.0 W
Lamp Current (Nom)	210 mA
Wattage Equivalent	60 W
Warm Up Time To 60% Light (Min)	5 s
Warm Up Time To 60% Light (Max)	40 s
Power Factor (Nom)	0.55
Voltage (Nom)	110-127 V

Controls and Dimming	
Dimmable	No

Approval and Application	
Mercury (Hg) Content (Max)	2 mg
Energy Consumption kWh/1000 h	13 kWh


Product Data	
Order product name	EL/mdTQS 13W GU24
EAN/UPC - Product	046677454197
Order code	454199

Energy Saver GU24

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689791101

Net Weight (Piece)	0.060 kg
--------------------	----------

Dimensional drawing



Product	D	C	F
EL/mdTQS 13W GU24	51.5 mm	95.0 mm	42.5 mm

TORNADO T2 13W/827 GU24 110-127V 50/60Hz

