



FLOODLIGHTS

**LED Swivel Floodlights
1000 Lumen 13W LED**

D23.2



Catalog #: LL1000Z

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
May be used with BELL® cluster covers and boxes

PRODUCT FEATURES

Rugged die cast construction
State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
Patented multi-directional swivel joint
Tempered Glass Lens
Long Life: 50,000 hours
Patented no-tool easy-mount feature
Warranty: 5 year
120V 60 Hz

UL LISTED

N/A

CULUS

File E464682

NEMA

3R Rated

NEC

2014 Compliant

US PATENTS

7,695,170

GENERAL PRODUCT INFORMATION

Color: Bronze

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.895

PACKAGING

Package Type: Clear Box
Std. Pkg.: 4
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 89.5
Ship Carton Length (in.): 17.38
Ship Carton Width (in.): 4.25
Ship Carton Height (in.): 4.75
Ctn Weight (Lbs.): 3.4
Pallet Qty: 1536
UPC Number: 050169917572
I2of5: 50050169917577