



Measurements:

<u>Height</u>	<u>Width</u>
6.00"	11.50"
<u>Max OAH</u>	
6.00"	
<u>Hanging Weight</u>	
2.01 lb	

Lamping:

Incandescent MB Incandescent	672 Rated Lumens
1.00 60W MB Incandescent	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.02 lb	11.81"	5.91"	11.81"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209583092	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB Incandescent (Not Included)