


NTS-5023

Front Loading Fresnel Lens with Specular Clear Reflector and Trim

DIMENSIONS



OD: 6-1/2"
Height: 5-3/4"

FEATURES

Trim

Precision spun 0.050 aluminum high grade specular clear reflector with high grade fresnel lens attached to trim. Easy lift and turn lens removal for re-lamping. Reflector includes two socket positions for optimum light control and output.

Note: Shallow housings must use lowest socket position.

Mounting

Trim includes two "V" torsion springs to mount trim securely to housing. Replacement "V" torsion springs are available (NRA-86).

Compatible Housings

Compatible with Line Voltage housings.
See individual specification sheets for more information.

Lamp

Line Voltage

25W A19 Maximum (NHIC-501QAT; NHRIC-504QAT)
35W PAR30 Maximum (NHIC-501QAT; NHIC-527QAT; NHRIC-504QAT; NHRIC-527QAT)
60W A19 Maximum (NH-501Q; NHR-504Q)

Labels and Listings

cULus Listed for Wet Location when used with Compatible Housings

Front Loading Fresnel Lens w/Specular Clear Reflector and Trim

NTS-5023W: Front Loading Fresnel Lens with Specular Clear Reflector and White Trim

Type


Project

Catalog No.


Lamp/Wattage

HOUSING DIMENSIONS


NH-501Q / NHIC-501QAT




NHIC-527QAT



NHR-504Q / NHRIC-504QAT



NHRIC-527QAT



Compatible Housings

LINE VOLTAGE

Item Number	Installation Type	Lamp	Dimensions
NH-501Q	Non-IC New Construction	60W A19	W: 7-1/4" L: 10-1/2" H: 7-1/2"
NHIC-501QAT	IC Air-Tight New Construction	35W or 25W	W: 7-1/4" L: 10-1/2" H: 7-1/2"
NHIC-527QAT	Shallow IC AT New Const.	35W PAR30	W: 7" L: 10-1/2" H: 5-7/8"
NHR-504Q	Non-IC Remodel Housing	60W A19	W: 5-1/2" L: 13-1/2" H: 7-1/2"
NHRIC-504QAT	IC Air-Tight Remodel Housing	35W or 25W	W: 5-1/2" L: 13-1/2" H: 7-1/2"
NHRIC-527QAT	Shallow IC AT Remodel	35W PAR30	W: 6-3/4" L: 13-1/4" H: 5-1/2"