



PAR38 LED

13PAR38/F35 2700 DIM SO

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.


Product data

General Information		Power (Rated) (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		13 W
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]	Lamp Current (Nom)	128 mA
Nominal Lifetime (Nom)	25000 h	Wattage Equivalent	90 W
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	13-90W	Warm Up Time To 60% Light (Max)	0.5 s
		Power Factor (Nom)	0.85
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	35 °		
Initial lumen (Nom)	900 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	900 lm	Dimmable	Yes
Luminous Intensity (Nom)	2450 cd		
Color Designation	Warm White (WW)	Approval and Application	
Rated Beam Angle	35 °	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	2700 K	Energy Efficiency Label (EEL)	Not applicable
Luminous Efficacy (rated) (Nom)	69 lm/W		
Color Consistency	<6	Product Data	
Color Rendering Index (Nom)	80	Order product name	120V PAR38 13W 35D 2700K 900 D SO
LLMF At End Of Nominal Lifetime (Nom)	70 %	EAN/UPC - Product	046677454746
Operating and Electrical		Order code	454744
Input Frequency	60 Hz	Numerator - Quantity Per Pack	1

PAR38 LED

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001132104
Net Weight (Piece)	0.001 kg

Dimensional drawing



PAR38 CL 120V 13W 35D 2700K E26 Dim

Product	D	C
---------	---	---

PAR38 LED

Photometric data

Accent Lighting - Spots

